Rittal – The System.

Faster – better – everywhere.



SK 2541.235

Integrated Louvers

State: 11/10/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 2541.235 - Integrated Louvers

For ventilation by convection, easily retro-fitted using 4 screws.

Features

Model No.	SK 2541.235
Product description	For ventilation by convection, easily retro-fitted using 4 screws.
Material	Carbon steel
Color	RAL 7035
Supply includes	Assembly components
Dimensions	Width: 160 mm Height: 110 mm Depth: 8 mm Width: 6.3 ″ Height: 4.33 ″ Depth: 0.31 ″
Packaging unit	4 pc(s).
Net weight	0.752 kg
Gross weight	0.9 kg
PCF/VE (cradle-to-gate)	3.5 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC000331
ETIM 8	EC000331
ECLASS 8.0	27189272
Product description	SK Integrated louvres, Sheet steel, WHD: 160 x 110 x 8 mm

© Rittal 2026