

Rittal – The System.

Faster – better – everywhere.



SK 2543.235 Integrated Louvers

State: 4/24/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 2543.235 - Integrated Louvers

For ventilation by convection, easily retro-fitted using 4 screws.

Features

Model No.	SK 2543.235
Product description	For ventilation by convection, easily retro-fitted using 4 screws.
Material	Carbon steel
Color	RAL 7035
Supply includes	Assembly components
Dimensions	Width: 330 mm Height: 110 mm Depth: 8 mm Width: 13 " Height: 4.33 " Depth: 0.31 "
Packaging unit	4 pc(s).
Net weight	1.568 kg
Gross weight	1.842 kg
PCF/VE (cradle-to-gate)	6.8 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC000331
ETIM 8	EC000331
ECLASS 8.0	27189272
Product description	SK Integrated louvres, Sheet steel, WHD: 330 x 110 x 8 mm