

Rittal – The System.

Faster – better – everywhere.



SK 3108.100 Enclosure internal fan

State: 6/29/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3108.100 - Enclosure internal fan

To prevent hot spots inside the enclosure and facilitate the ventilation of active enclosure climate control components.



Features

Model No.	SK 3108.100
Product description	To prevent hot-spots and support the air routing of active enclosure climate control components. Adjustable in two axes. Mounted on the frame section. Several fans can be cascaded using the quick-release terminal strip.
Supply includes	Complete unit ready for connection with axial fan Snap-on pivot device Fasteners
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 19 W At 60 Hz: 18 W
Rated current max.	At 50 Hz: 0.12 A At 60 Hz: 0.11 A
Packaging unit	1 pc(s).
Net weight	0.94 kg
Gross weight	1.126 kg
Customs tariff number	84145915
ETIM 9	EC000320

Features

ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK enclosure internal fan, 19/18 W, 230 V, 1~, 50/60 Hz

Approvals

Explanations	Declaration of conformity
--------------	---------------------------
