## Rittal – The System.

Faster – better – everywhere.





# SK 3110.000 **Thermostat**

State: 12/9/2025 (Source: rittal.com/us-en)



#### SK 3110.000 - Thermostat Internal Enclosure Thermostat

Suitable for controlling fan units, heaters, and heat exchangers. This thermostat can also be used as a signal generator for monitoring the internal enclosure temperature.

#### **Features**

Model No.	SK 3110.000
Product description	Suitable for controlling fan units, heaters and heat exchangers. This thermostat can also be used as a signal generator for monitoring the internal enclosure temperature.
Benefits	Time-saving connection technique using a terminal strip with a screw connection from the outside.  Flexible mounting on a vertical or horizontal 35 mm support rail to EN 50 022, snap fastening in the enclosure section or on the mounting plate using the supplied adapter.
Technical specifications	Bi-metal controller as a temperature-sensitive element with thermal feedback Contact population: Single-pole change-over contact as a quick-break contact Permissible contact load: Category 5 – 3 (heating): AC 10 (4) A (inductive load at $\cos \phi = 0.6$ ) / $\cot \phi = 0.6$ / $\cot \phi = 0.6$ / Category 5- 4 (cooling): AC 5 (4) A (inductive load at $\cos \phi = 0.6$ ) / DC = $\cot \phi = 0.6$ / DC = $\cot \phi = 0.6$ / Switching difference: approx. 1 K ± 0.8 K.
Color	RAL 7035
Packaging unit	1 pc(s).
Dimensions	Width: 71 mm  Height: 71 mm  Depth: 33.5 mm  Width: 2.8 "  Height: 2.8 "  Depth: 1.32 "
Setting range	5 °C60 °C 41 °F140 °F
Rated operating voltage	24 V - 230 V, 1~ 24 V - 60 V (DC)

© Rittal 2025

2

### Features

Net weight	0.095
Gross weight	0.12
Customs tariff number	90321020
EAN	4028177036598
E-Number Sweden	E3404752
ETIM 9	EC004587
ETIM 8	EC004587
ECLASS 8.0	27210707

## **Approvals**

Approvals	UL + C-UL (listed) VDE
Certificates	EAC
Explanations	Declaration of conformity  Declaration of conformity UK

© Rittal 2025 3