

**Rittal – The System.**

Faster – better – everywhere.



**SK 3114.200**

**Digital enclosure internal  
temperature display and thermostat**

State: 6/9/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3114.200 - Digital enclosure internal temperature display and thermostat

For installation in the enclosure door or wall.

## Features

Model No.	SK 3114.200
Product description	For installation in the enclosure door or wall.
Technical specifications	Three-digit, 7-segment display Option of switching between °C/°F. With 1800 mm long NTC sensor Two relay outputs as change-over contact and normally open contact (max. contact load 230 V, 6 A). Freely selectable switching difference.
Color	RAL 7035
Packaging unit	1 pc(s).
Operating temperature range	0 °C...50 °C 32 °F...122 °F
Setting range	5 °C...55 °C 41 °F...131 °F
Rated operating voltage	100 V - 230 V, 1~, 50 Hz/60 Hz 24 V - 60 V (DC)
Storage temperature range	-20 °C...70 °C -4 °F...158 °F
Protection category IP to IEC 60529	IP 54
Net weight	0.258 kg
Gross weight	0.259 kg
Customs tariff number	90321020
ETIM 9	EC004587
ETIM 8	EC004587

# Features

---

ECLASS 8.0	27210707
------------	----------

---

Product description	SK Digital enclosure internal , temperature display and thermostat, 100-230 V, 1~, 50/60 Hz, 24-60 V (DC), Installation depth: 100 mm
---------------------	---

# Approvals

---

Approvals	UR
-----------	----

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---