Rittal – The System.

Faster – better – everywhere.





SK 3126.115 TopTherm air-air heat exchanger

State: 11/9/2025 (Source: rittal.com/us-en)



SK 3126.115 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

Features

Model No.	SK 3126.115
Version	wall-mounted
Product description	Air-to-air heat exchangers are especially suitable for aggressive environments since the internal and external circuit are completely separated from each other by two air circuits.
Color	RAL 7035
Supply includes	Complete unit ready for connection
	Plug-in terminal strip
	Floating fault signal contact in case of overtemperature
	Drilling template
	Fasteners
Specific thermal output	17.5 W/K
Air throughput (unimpeded air	External circuit at 50 Hz: 265 m³/h
flow)	External circuit at 60 Hz: 315 m³/h
	Internal circuit at 50 Hz: 265 m³/h
	internal circuit at 60 Hz. 200 Hi / II
	Internal circuit at 60 Hz: 315 m³/h
	Internal circuit at 60 Hz: 315 m³/h
	Internal circuit at 60 Hz: 315 m³/h External circuit at 50 Hz: 156 cfm
	Internal circuit at 60 Hz: 315 m³/h External circuit at 50 Hz: 156 cfm External circuit at 60 Hz: 185.4 cfm
Rated operating voltage	Internal circuit at 60 Hz: 315 m³/h External circuit at 50 Hz: 156 cfm External circuit at 60 Hz: 185.4 cfm Internal circuit at 50 Hz: 156 cfm
Rated operating voltage Rated current max.	Internal circuit at 60 Hz: 315 m³/h External circuit at 50 Hz: 156 cfm External circuit at 60 Hz: 185.4 cfm Internal circuit at 50 Hz: 156 cfm Internal circuit at 60 Hz: 185.4 cfm

© Rittal 2025 2

Features

Dimensions	Width: 280 mm		
	Height: 550 mm		
	Depth: 150 mm Width: 11 " Height: 21.7 " Depth: 5.91 "		
		Pre-fuse	Miniature circuit-breaker/fuse: 2 A
		Temperature control	Electronic Control with Digital Display (factory setting +35 °C)
		Operating temperature range	-5 °C55 °C
	23 °F131 °F		
Protection category IP to IEC 60	Internal circuit, IP 54		
529	External circuit, IP 34		
Packaging unit	1 pc(s).		
Net weight	8.94		
Gross weight	9.54		
Customs tariff number	84158300		
EAN	4028177425088		
ETIM 9	EC002514		
ETIM 8	EC002514		
ECLASS 8.0	27180711		

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3