Rittal – The System.

Faster – better – everywhere.



SK 3130.115

TopTherm air-air heat exchanger

State: 11/18/2026 (Source: www.rittal.com/us-en)

SK 3130.115 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

Features

Model No.	SK 3130.115
Version	wall-mounted
Product description	Air-to-air heat exchangers are especially suitable for aggressive environments since the internal and external circuit are completely separated from each other by two air circuits.
Color	RAL 7035
Supply includes	Complete unit ready for connection Plug-in terminal strip Floating fault signal contact in case of overtemperature Drilling template Fasteners
Specific thermal output	90 W/K
Air throughput (unimpeded air flow)	External circuit at 50 Hz: 850 m³/h External circuit at 60 Hz: 945 m³/h Internal circuit at 50 Hz: 850 m³/h Internal circuit at 60 Hz: 945 m³/h External circuit at 50 Hz: 500.3 cfm External circuit at 60 Hz: 556.2 cfm Internal circuit at 50 Hz: 500.3 cfm Internal circuit at 60 Hz: 556.2 cfm
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Dimensions	Width: 400 mm Height: 1,580 mm Depth: 215 mm Width: 15.7 ″ Height: 62.2 ″ Depth: 8.46 ″
Pre-fuse	Miniature circuit-breaker/fuse: 4 A

© Rittal 2026

Features

Temperature control	Electronic Control with Digital Display (factory setting +35 °C)
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Protection category IP to IEC 60 529	Internal circuit, IP 54 External circuit, IP 34
Packaging unit	1 pc(s).
Net weight	24.1 kg
Gross weight	24.95 kg
CRA risk class	Default (Low Risk)
Customs tariff number	84158300
ETIM 9	EC002514
ETIM 8	EC002514
ECLASS 8.0	27180711
Product description	SK Air/air heat exchanger TopTherm, wall-mounted, 90 W/K, 115 V, 50/60 Hz, HWD: 1580 x 400 x 215 mm

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK