

Rittal – The System.

Faster – better – everywhere.



SK 3237.124

TopTherm Filter Fan Units

State: 1/5/2026 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3237.124 - TopTherm Filter Fan Units

Complete fan unit for tool-free mounting on surfaces. Air throughput from 11.77 - 529.72 cfm, protection category IP 54 as standard.

Features

Model No.	SK 3237.124
Version	wall-mounted
Product description	Filter fans with diagonal fan technology are more pressure-resistant and produce more constant air performance. The diagonal outflow direction ensures a more uniform heat dissipation from the enclosure.
Product modification	Since May 2024, the cover for the connection terminal is no longer part of the TopTherm filter fan. During testing, it was found not to be required by the standards and does not impair function or operational safety.
Color	RAL 7035
Supply includes	Complete unit ready to install, including chopped fiber filter mat
Fan	Axial, DC motor
Unimpeded air flow (with chopped fiber filter)	with DC: 20 m³/h
Air throughput with outlet filter incl. chopped fiber filter mat (quantity x order number)	1 x 3237200: 15 m³/h 2 x 3237200: 16 m³/h
Rated operating voltage	24 V (DC)
Rated power Pel	with DC: 2.4 W
Rated current max.	with DC: 0.1 A
Dimensions	Width: 116.5 mm Height: 116.5 mm Width: 4.59 " Height: 4.59 "

Features

Installation depth	43 mm 1.69 "
Mounting cut-out	Width of opening: 92 mm Cut-out height: 92 mm Width of opening: 3.62 " Cut-out height: 3.62 "
Protection category IP to IEC 60 529	IP 54 with fleece filter IP 56 with fleece filter and hose-proof hood
Protection category NEMA	Type 12 with fleece filter Type 3 Type 3R with fleece filter and hose-proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Note	A pleated filter can optionally be used to increase the air throughput (see characteristic curve). This can be used with both the filter & roof-mounted fans and the exhaust filters. For the 3237.XXX filter fan, the electrical connection is made via 2 individual wires (length approx. 300 mm) on the unit, for all other filter fans, it's made via a spring-loaded terminal
Operating temperature range	-15 °C...55 °C 5 °F...131 °F
Storage temperature range	-30 °C...70 °C -22 °F...158 °F
Noise pressure level	with DC: 38 dB(A)
Packaging unit	1 pc(s).
Net weight	0.28
Gross weight	0.3
Customs tariff number	84145915
EAN	4028177651609
E-Number Sweden	E3404337
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Approvals

CSA

30 - KC Korea

UL + C-UL - FTTA

UR + C-UR (recognized)

Explanations

Declaration of conformity