

Rittal – The System.

Faster – better – everywhere.



SK 3237.610

TopTherm Filter Fan Units

State: 6/19/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3237.610 - TopTherm Filter Fan Units EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 11.77 - 529.72 cfm, standard protection category IP 54.



Features

| | |
|-------------------------------------|---|
| Model No. | SK 3237.610 |
| Version | EMC |
| Color | RAL 7035 |
| Supply includes | Complete unit ready for connection, including filter mat |
| Rated current max. | At 50 Hz: 0.12 A At 60 Hz: 0.13 A |
| Mounting cut-out | Width of opening: 92 mm Cut-out height: 92 mm Width of opening: 3.62 " Cut-out height: 3.62 " |
| EMC version | Yes |
| Fan | Axial, shaded pole motor |
| At 60 Hz | 0.13 A |
| Note | For energy-efficient operation of the filter fan units, we recommend using the enclosure internal thermostat, the speed control or the digital enclosure internal temperature display and thermostat. |
| Air throughput (unimpeded air flow) | At 50 Hz: 20 m ³ /h At 60 Hz: 25 m ³ /h At 50 Hz: 11.8 cfm At 60 Hz: 14.7 cfm |

Features

| | |
|-------------------------------------|--|
| Dimensions | Width: 116.5 mm Height: 116.5 mm Width: 4.59 " Height: 4.59 " |
| Protection category IP to IEC 60529 | IP 54 IP 56 |
| Operating temperature range | -15 °C...55 °C 5 °F...131 °F |
| Pre-fuse | Miniature circuit-breaker/fuse: 2 A |
| Storage temperature range | -30 °C...70 °C -22 °F...158 °F |
| Rated power Pel | At 50 Hz: 11 W At 60 Hz: 9 W |
| Noise pressure level | At 50 Hz: 38 dB(A) At 60 Hz: 43 dB(A) |
| Packaging unit | 1 pc(s). |
| Net weight | 1.06 lb |
| Gross weight | 1.06 lb |
| Customs tariff number | 8414590099 |
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Product description | EMC filter fan 20m ³ /h 115V 50/60Hz, width x height 116.5 x 116.5 mm |

Approvals

| | |
|-----------|---|
| Approvals | Approvals UL + C-UL - FTTA UR + C-UR (recognized) |
|-----------|---|

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK