## Rittal – The System.

Faster - better - everywhere.





# SK 3237.700 Blue e+ filter fan


State: 11/19/2025 (Source: rittal.com/us-en)



#### SK 3237.700 - Blue e+ filter fan

Complete fan unit for tool-free mounting on surfaces. Air throughput from 11 - 682.75 cfm, protection category IP 54 as standard.







#### **Features**

Model No.	SK 3237.700
Version	wall-mounted
Product description	Filter fans with diagonal fan technology are more pressure-resistant and produce more constant air performance. The diagonal outflow direction ensures a more uniform heat dissipation from the enclosure.
Benefits	Easy filter change thanks to a new opening mechanism on the louvre grille Faster assembly on the enclosure due to optimized snap hooks Diagonal fan technology ensures more uniform and consistent ventilation of the control cabinet through higher pressure stability. Tool-free mounting
Material	Plastic
Color	RAL 7035
Supply includes	Complete unit ready to install, including chopped fiber filter mat
Fan	Axial, shaded pole motor

© Rittal 2025 2

### Features

At 50 Hz: 20 m³/h
At 60 Hz: 25 m³/h
At 50 Hz: 11.8 cfm At 60 Hz: 14.7 cfm
At 60 Hz. 14.7 cm
At 50 Hz: 15 m³/h
At 60 Hz: 18 m³/h
At 50 Hz: 8.83 cfm
At 60 Hz: 10.59 cfm
230 V, 1~, 50 Hz/60 Hz
At 50 Hz: 13 W
At 60 Hz: 11.1 W
At 50 Hz: 0.1 A
At 60 Hz: 0.09 A
Width: 116.5 mm
Height: 116.5 mm
Depth: 64.5 mm
Width: 4.59 ″
Height: 4.59 "
Depth: 2.54 "
46 mm
1.81 ″
Width of opening: 92 mm
Cut-out height: 92 mm
Width of opening: 3.62 "
Cut-out height: 3.62 "
IP 54 with fleece filter
IP 56 with fleece filter and hose-proof hood
Type 12 with fleece filter
Type 3, 3R with fleece filter and hose-proof hood
Miniature circuit-breaker/fuse: 2 A
For the 3237.XXX filter fan, the electrical connection is made via 2
individual wires (length approx. 300 mm) on the unit, for all other
filter fans, it's made via a spring-loaded terminal
-15 °C55 °C
5 °F131 °F

© Rittal 2025 3

## Features

Storage temperature range	-30 °C70 °C
	-22 °F158 °F
Noise pressure level	At 50 Hz: 42 dB(A)
	At 60 Hz: 47 dB(A)
Packaging unit	1 pc(s).
Net weight	0.462
Gross weight	0.464
Customs tariff number	84145915
EAN	4028177997776
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

## **Approvals**

Approvals	CSA 30 - KC Korea
	UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025