Rittal – The System.

Faster – better – everywhere.






SK 3140.140 Roof-mounted fan, roof vent

State: 11/8/2025 (Source: rittal.com/us-en)



SK 3140.140 - Roof-mounted fan, roof vent

The new generation of roof-mounted fans is one system for all sizes: only one mounting cut-out is needed for all output categories. Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54.







Features

Model No.	SK 3140.140
Version	roof-mounted
Product description	Roof-mounted fan with a high protection category and flexible installation from the inside or outside.
Color	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	Radial, rotary current motor
Unimpeded air flow (with pleated	At 50 Hz: 800 m³/h
filter)	At 60 Hz: 853 m³/h
	At 50 Hz: 470.86 cfm
	At 60 Hz: 502.06 cfm
Unimpeded air flow (without filter	At 50 Hz: 863 m³/h
mats)	At 60 Hz: 942 m³/h
	At 50 Hz: 507.94 cfm
	At 60 Hz: 554.44 cfm

© Rittal 2025 2

Features

1 x 3243200: 555/565 m³/h 2 x 3243200: 660/685 m³/h
1 x 3243200: 575/600 m³/h
380 V - 415 V, 3~, 50 Hz/60 Hz 400 V - 480 V, 3~, 60 Hz
At 50 Hz: 98 W At 60 Hz: 130 W
At 50 Hz: 0.17 A At 60 Hz: 0.2 A
Width: 400 mm Height: 133 mm Depth: 400 mm Width: 15.7 " Height: 5.24 " Depth: 15.7 "
34.6 mm 1.36 ″
Width of opening: 258 mm Depth of opening: 258 mm Width of opening: 10.2 " Depth of opening: 10.2 "
IP 21 without filter mat IP 54 including pleated filter
NEMA 12
A chopped fiber filter can be used to increase the protection category to IP 55 (see accessories). To improve energy efficiency and increase equipment service life, we recommend thermostats or temperature displays.
At 50 Hz: 63,500 h
At 60 Hz: 61,500 h

© Rittal 2025

Features

Storage temperature range	-40 °C70 °C
	-40 °F158 °F
Noise pressure level	At 50 Hz: 56 dB(A)
	At 60 Hz: 58 dB(A)
Packaging unit	1 pc(s).
Net weight	6
Gross weight	6.02
Customs tariff number	84145915
EAN	4028177709133
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
ECLASS 8.0	27180716

Approvals

Approvals	CSA
	IEC CB
	30 - KC Korea
	TÜV-certified safety
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025