

# Rittal – The System.

Faster – better – everywhere.



## SK 3238.080 Hose-proof hood

State: 4/25/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3238.080 - Hose-proof hood Stainless steel

The Rittal stainless steel fan shroud is engineered for rugged indoor and outdoor use. Its durable finish carries UL Type 3R and 4X certifications (model 3237 Type 12, 3R only) to guard against large debris, heavy rain, hose-directed water sprays, and corrosion. A blue silicone gasket—rooted in Rittal's Food & Beverage expertise—ensures superior hygiene and simplifies washdown cleaning.



## Features

|                          |   |
|--------------------------|---|
| Model No.                | SK 3238.080   |
| Product description      | For fan-and-filter units/outlet filters. Easy cleaning thanks to external, food-safe silicone seal. |
| Material                 | Stainless steel AISI304 - 1.4301 (V2A)<br>Silicone  |
| Suitable for Model No.   | 3238....  |
| Dimensions               | Width: 176 mm<br>Height: 245 mm<br>Depth: 55 mm<br>Width: 6.93 "<br>Height: 9.65 "<br>Depth: 2.17 " |
| Protection category NEMA | NEMA 1<br>NEMA 12<br>NEMA 3<br>NEMA 3R<br>NEMA 4<br>NEMA 4X   |

# Features

---

|                                     |  |
|-------------------------------------|--|
| Protection category IP to IEC 60529 | IP 56 when fitted over fan-and-filter unit/outlet filter with filter mat |
| Packaging unit                      | 1 pc(s).   |
| Net weight                          | 1.23 kg  |
| Gross weight                        | 1.358 kg   |
| Customs tariff number               | 73269098   |
| ETIM 9                              | EC000744   |
| ETIM 8                              | EC000744   |
| ECLASS 8.0                          | 27182405   |
| Product description                 | SK hose-proof hood, for SK 3238..., WHD: 176 x 245 x 55 mm               |

# Approvals

---

|           |   |
|-----------|---|
| Approvals | CSA<br>UL + C-UL - FTTA<br>UR + C-UR (recognized) |
|-----------|---|