Rittal – The System.

Faster - better - everywhere.





SK 3238.200 Outlet Filters

State: 12/1/2025 (Source: rittal.com/us-en)



SK 3238.200 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



Features

SK 3238.200
For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
ABS
RAL 7035
Outlet Filters
Chopped fiber filter mat
Width of opening: 124 mm
Cut-out height: 124 mm
Width of opening: 4.88 "
Cut-out height: 4.88 "
SK 3238.1xx
Width: 148.5 mm
Height: 148.5 mm
Depth: 24 mm
Width: 5.85 "
Height: 5.85 ″
Depth: 0.94 "

© Rittal 2025

Features

Protection category NEMA	Type 1 with pleated filter
	Type 12 with fleece filter
	Type 3
	Type 3R
	Type 4
	Type 4X with chopped fiber filter/pleated filter and hose-proof hood
Protection category IP to IEC 60	IP 54 with chopped fiber filter/pleated filter
529	IP 55 with pleated filter and absorber mat
	IP 56 with chopped fiber filter/pleated filter and hose-proof hood
Packaging unit	1 pc(s).
Net weight	0.17
Gross weight	0.18
Customs tariff number	39269097
EAN	4028177651739
E-Number Sweden	E3404349
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	CSA
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity

© Rittal 2025 3