

Rittal – The System.

Faster – better – everywhere.



SK 3184.800

Wall-mounted cooling unit Blue e+ S

State: 8/31/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3184.800 - Wall-mounted cooling unit Blue e+ S

1023.64 - 3412.14 BTU/h

Blue e+ S cooling units with proven Blue e+ technology offer the world's highest energy efficiency. This is also linked with a reduction in the CO₂ footprint of machinery and equipment. In a new design and with many smart functions.

Features

Model No.	SK 3184.800
Version	wall-mounted
Benefits	Helps make production climate-neutral thanks to average energy savings of 75% and reduction of CO ₂ footprint Increased environmental friendliness through use of refrigerant R-513A Universal compatibility due to multi-voltage capability and country-specific approvals Intelligent and easy monitoring via IoT interface Convenient operation with the Rittal Scan & Service App
Material	Carbon steel
General color	RAL 7035
Color	Housing: RAL 7035 Louvered grille: RAL 7012
Supply includes	Assembly components Wired ready for connection (plug-in terminal strip) Integral electric condensate evaporation
Options	For remote monitoring and networking of cooling units and chillers, use the Blue e+ Generation IoT Interface, item number 3124.300. Increase machine availability and process safety by remote monitoring of device data, condition, and system messages.

Features

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 1 kW Cooling output L35 L35/60 Hz: 1 kW Cooling output L35 L50/50 Hz: 0.6 kW Cooling output L35 L50/60 Hz: 0.6 kW Cooling output L35 L35/50 Hz: 3,412 BTU/h Cooling output L35 L35/60 Hz: 3,412 BTU/h Cooling output L35 L50/50 Hz: 2,047 BTU/h Cooling output L35 L50/60 Hz: 2,047 BTU/h
Rated operating voltage	110 V - 240 V, 1~, 50 Hz/60 Hz
Note	Please observe the assembly instructions. When the software is downloaded, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these license conditions. Only for semi-outdoor use (see instructions for description)
Note on Model No.:	Tolerance: 110 V -10% (99 V) and 240 V +10% (264 V)
Rated output	0.6 kW
Air throughput (unimpeded air flow)	External circuit: 680 m³/h Internal circuit: 680 m³/h External circuit: 400.2 cfm Internal circuit: 400.2 cfm
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.4 Refrigeration factor L35 L35 (EER) 60 Hz: 2.4
Version	wall-mounted
Dimensions	Width: 400 mm Height: 950 mm Depth: 196 mm Width: 15.7 " Height: 37.4 " Depth: 7.72 "
Required mounting cut-out	Width of opening: 383 mm Cut-out height: 929 mm Width of opening: 15.1 " Cut-out height: 36.6 "
Protection category IP to EN 60 529	Internal circuit IP 55

Features

Protection category NEMA	UL Type 12 UL Type 3R
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.31 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.2 t Refrigerant: R-513A Quantity: 0.7 lb.
Temperature control	e+ controller (factory setting +35 °C)
Operating temperature range	-20 °C...60 °C -4 °F...140 °F
Storage temperature range	-40 °C...70 °C -40 °F...158 °F
Operating temperature range of refrigerant circuit (active)	3 °C...60 °C
Operating temperature range of heat pipe	-20 °C...45 °C
Setting range	20 °C...50 °C 68 °F...122 °F
Rated power Pel	Rated power L35 L35/50 Hz: 0.42 kW Rated power L35 L35/60 Hz: 0.42 kW Rated power L35 L50/50 Hz: 0.48 kW Rated power L35 L50/60 Hz: 0.48 kW
Permissible operating pressure (p. max.)	34 bar 493.1 PSI
Packaging unit	1 pc(s).
Net weight	26.5
Gross weight	31.5
Customs tariff number	84158200
EAN	4028177949973
ETIM 9	EC000855
ETIM 8	EC000855

Features

ECLASS 8.0	27180704
------------	----------

Approvals

Approvals	30 - KC Korea UL + C-UL (listed) UL + C-UL - FTTA
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK
