

Rittal – The System.

Faster – better – everywhere.



SK 3201.840

Modular climate control concept – climate control door VX25

State: 6/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3201.840 - Modular climate control concept – climate control door VX25 for installing cooling modules

Carbon steel climate control doors for the installation of air conditioning modules of types SK 3307.7XX to 3310.7XX.

Features

Model No.	SK 3201.840
Product description	Carbon steel climate control doors for the installation of air conditioning modules of types SK 3307.7XX to 3310.7XX. The climate control doors fit perfectly with the overall design of the enclosure.
Material	Carbon steel
Color	RAL 7035
Supply includes	Climate control door without preconfigured cooling module 180° hinges, door opening angle approx. 130°
Note on Model No.:	Suitable for VX enclosures For 1200 mm wide VX enclosures, the existing hinged door may be used, irrespective of the device position (left or right) Door hinged on left
Suitable for	Device positioned on the left
Suitable for	Enclosure type: VX: = 600 mm: = 1,800 mm Enclosure type: = 1,200 mm Enclosure type: VX: = 23.6 " : = 70.9 " Enclosure type: = 47.2 "
Packaging unit	1 pc(s).
Net weight	25.7 kg
Gross weight	26.8 kg
Customs tariff number	94039910
ETIM 9	EC002510
ETIM 8	EC002510

Features

ECLASS 8.0

27180702

Product description

SK climate control door for cooling module,, for VX25 600/1200 mm wide, 1800 mm high, door hinge left

Approvals

Explanations

Declaration of conformity - F-gas regulation