

# Rittal – The System.

Faster – better – everywhere.



## SK 3240.400 Blue e+ outlet filter

State: 7/6/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3240.400 - Blue e+ outlet filter EMC

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



## Features

|                        |   |
|------------------------|---|
| Model No.              | SK 3240.400   |
| Version                | wall-mounted<br>EMC   |
| Benefits               | Easy filter change thanks to a new opening mechanism on the louvre grille<br>Faster assembly on the enclosure due to optimized snap hooks<br>Tool-free mounting |
| Color                  | RAL 7035  |
| Supply includes        | Outlet Filters<br>EMC Filter Mat  |
| Mounting cut-out       | Width of opening: 224 mm<br>Cut-out height: 224 mm<br>Width of opening: 8.82 "<br>Cut-out height: 8.82 "  |
| Suitable for Model No. | SK 3240.8xx/3241.8xx  |

## Features

|                                     |   |
|-------------------------------------|---|
| Dimensions                          | Width: 255 mm<br>Height: 255 mm<br>Depth: 45.2 mm<br>Width: 10 "<br>Height: 10 "<br>Depth: 1.78 " |
| Protection category NEMA            | Type 12 with fleece filter<br>Type 3, 3R, 4, 4X with fleece filter and hose-proof hood            |
| Protection category IP to IEC 60529 | IP 54 with fleece filter<br>IP 56 with fleece filter and hose-proof hood                          |
| Packaging unit                      | 1 pc(s).  |
| Net weight                          | 0.4   |
| Gross weight                        | 0.661   |
| Customs tariff number               | 39269097  |
| EAN                                 | 4028177998346   |
| ETIM 9                              | EC002513  |
| ETIM 8                              | EC002513  |
| ECLASS 8.0                          | 27180706  |

## Approvals

|           |  |
|-----------|--|
| Approvals | UL + C-UL - FTTA<br>UR + C-UR (recognized) |
|-----------|--|