

Rittal – The System.

Faster – better – everywhere.



SK 3215.700

Air-Water Heat Exchangers

State: 4/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3215.700 - Air-Water Heat Exchangers Wall-mounted HD

Air/water heat exchanger for production areas in the food and beverage industry where hygiene is important – the perfect addition to the Rittal Hygienic Design range. The easy-to-clean design reduces the risk of contamination and ensures food safety.



Features

Model No.	SK 3215.700
Version	Water-carrying parts copper/brass (Cu/CuZn)
Product description	Air/water heat exchanger for production areas in the food sector with high hygienic requirements – the ideal supplement to the Rittal Hygienic Design Program. Its easy-clean design reduces the risk of contamination and guarantees food safety.
Benefits	Easy-clean and hygiene-compliant design A roof slope of 30° prevents objects from being placed on them and allows liquid to run off quickly An all-round external, replaceable silicone seal prevents the build-up of dirt between the enclosure and the air-water heat exchanger.
Material	Housing: Stainless steel 1.4301 (AISI 304)
Surface finish	Housing: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Wired ready for connection Drilling template Sealing and assembly components

Features

Total cooling output	L 35 W 10 at 200 l/h: 1 kW L 35 W 10 at 400 l/h: 1.2 kW L 35 W 10 at 200 l/h: 3,412 BTU/h L 35 W 10 at 400 l/h: 4,095 BTU/h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 77 W At 60 Hz: 104 W
Rated current max.	At 50 Hz: 0.38 A At 60 Hz: 0.47 A
Permissible operating pressure (p. max.)	1 - 10 bar 14.5 - 145 PSI
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)
Water inlet temperature	1 °C...30 °C 34 °F...86 °F
Water connections	G 3/8" external thread
Temperature control	Thermostat-controlled solenoid valve
Temperature monitoring	Internal thermostat, with change-over contact, switching load 16 A, setting range +20 °C ... +60 °C (factory setting +35 °C)
Operating temperature range	1 °C...70 °C 34 °F...158 °F
Dimensions	Width: 215 mm Height: 982 mm Depth: 100 mm Width: 8.46 " Height: 38.7 " Depth: 3.94 "
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Setting range	20 °C...60 °C 68 °F...140 °F
Protection category IP to EN 60529	IP 56/59

Features

Protection category NEMA	NEMA 4X
Packaging unit	1 pc(s).
Net weight	14 kg
Gross weight	14 kg
Customs tariff number	84158300
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	SK Air/water heat exchanger, wall-mounted, 4095 BTU/h 230 V, 1~, 50/60 Hz, Thermostat-controlled magnetic valve, WHD: 215 x 982 x 100 mm

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity