### Rittal - The System.

Faster – better – everywhere.





# SK 3235.440 EC speed control

State: 11/17/2025 (Source: rittal.com/us-en)



## SK 3235.440 - EC speed control Control unit for EC fans

Temperature-dependent speed control for EC- filter fan for noise reduction and energy conservation .

#### **Features**

Model No.	SK 3235.440
Product description	Temperature-dependent speed control for EC fans for noise
	reduction and energy conservation. The fan function can also be monitored.
Function principle	Activation and monitoring of up to 4 EC filter fans
	For mounting on a 35 mm support rail EN 50 022
	External temperature sensor for monitoring the actual temperature
	Status LED for displaying the operating condition
	Alarm relay for signaling overtemperature, fan fault, line
	disconnection and sensor failure
Supply includes	Speed Control
	NTC sensor, length 1.80 m
Packaging unit	1 pc(s).
Speed	100 %
Suitable for Model No.	3140.500
	3140.510
	3240.500
	3241.500
	3243.500
	3244.500
	3245.500
	3245.510
	3245.508
	3245.518
Setting range	5 °C55 °C
	41 °F131 °F
Rated operating voltage	100 V - 250 V, 50 Hz/60 Hz
Net weight	0.45

© Rittal 2025

#### **Features**

Gross weight	0.51
Customs tariff number	90328900
EAN	4028177670716
ETIM 9	EC000256
ETIM 8	EC000256
ECLASS 8.0	27142320

## **Approvals**

Approvals	C-UR
	UR
	UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity

© Rittal 2025 3