

Rittal – The System.

Faster – better – everywhere.



SK 3238.124

TopTherm Filter Fan Units

State: 5/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3238.124 - TopTherm Filter Fan Units

Complete fan unit for tool-free mounting on surfaces. Air throughput from 11.77 - 529.72 cfm, protection category IP 54 as standard.

Features

Model No.	SK 3238.124
Version	wall-mounted
Product description	Filter fans with diagonal fan technology are more pressure-resistant and produce more constant air performance. The diagonal outflow direction ensures a more uniform heat dissipation from the enclosure.
Product changes	Since May 2024, the cover for the connection terminal is no longer part of the TopTherm filter fan. During testing, it was found not to be required by the standards and does not impair function or operational safety.
Color	RAL 7035
Supply includes	Complete unit ready to install, including chopped fiber filter mat
Fan	Axial, DC motor
Unimpeded air flow (with pleated filter)	with DC: 63 m ³ /h
Unimpeded air flow (with chopped fiber filter)	with DC: 52 m ³ /h
Air throughput with outlet filter incl. chopped fiber filter mat (quantity x order number)	1 x 3238200: 36 m ³ /h 2 x 3238200: 46 m ³ /h
Rated operating voltage	24 V (DC)
Rated power Pel	with DC: 5.7 W
Rated current max.	with DC: 0.24 A

Features

Dimensions	Width: 148.5 mm Height: 148.5 mm Width: 5.85 ″ Height: 5.85 ″
Installation depth	58.5 mm 2.3 ″
Mounting cut-out	Width of opening: 124 mm Cut-out height: 124 mm Width of opening: 4.88 ″ Cut-out height: 4.88 ″
Protection category IP to IEC 60529	IP 54 with chopped fiber filter/pleated filter IP 56 with chopped fiber filter/pleated filter and hose-proof hood
Protection category NEMA	Type 12 with chopped fiber filter/pleated filter Type 3 Type 3R Type 4 Type 4X with chopped fiber filter/pleated filter and hose-proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Note	A pleated filter can optionally be used to increase the air throughput (see characteristic curve). This can be used with both the filter & roof-mounted fans and the exhaust filters. For the 3237.XXX filter fan, the electrical connection is made via 2 individual wires (length approx. 300 mm) on the unit, for all other filter fans, it's made via a spring-loaded terminal
Operating temperature range	-15 °C...55 °C 5 °F...131 °F
Storage temperature range	-30 °C...70 °C -22 °F...158 °F
Noise pressure level	with DC: 46 dB(A)
Packaging unit	1 pc(s).
Net weight	0.539 kg
Gross weight	0.64 kg
Customs tariff number	84145915
ETIM 9	EC000320

Features

ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK Fan-and-filter unit TopTherm, 30.6 cfm 24 V (DC), WHD: 148.5 x 148.5 x 16 mm

Approvals

Approvals	CSA 30 - KC Korea UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity
