

**Rittal – The System.**

Faster – better – everywhere.



**SK 3301.505**

**Electric condensate evaporator**

State: 7/8/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3301.505 - Electric condensate evaporator

For external mounting on enclosures. For use with all enclosure cooling units and air/water heat exchangers (wall-mounted).



## Features

Model No.	SK 3301.505
Product description	For external mounting on enclosures. For use with all enclosure cooling units and air/water heat exchangers (wall-mounted).
Benefits	Suitable for international use thanks to multi-voltage support
Color	RAL 7035
Supply includes	Electric condensate evaporator, ready to connect.
Evaporation performance	230 V: 3,5 l/d 115 V: 3.0 L/d
Dimensions	Width: 400 mm Height: 129 mm Depth: 105 mm Width: 15.7 " Height: 5.08 " Depth: 4.13 "
Operating temperature range	5 °C...60 °C 41 °F...140 °F
Rated operating voltage	115 V - 230 V, 1~, 50 Hz/60 Hz
Packaging unit	1 pc(s).
Net weight	1.74 kg
Gross weight	2.2 kg

# Features

---

Customs tariff number	84189910
ETIM 9	EC002009
ETIM 8	EC002009
ECLASS 8.0	27180715
Product description	SK Electric condensate evaporator, 115-230 V, 1~, 50/60 Hz, WHD: 400 x 129 x 105 mm

---

# Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------