

Rittal – The System.

Faster – better – everywhere.



SK 3304.518

**TopTherm Blue e Wall-Mounted
Cooling Unit, UL Type 3R/4**

State: 6/15/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3304.518 - TopTherm Blue e Wall-Mounted Cooling Unit, UL Type 3R/4 1706.07 - 8530.36 BTU/h

Energy-efficient Blue e wall-mounted cooling units in output categories 1706.07 - 8530.36 BTU/h with e-Comfort controller and electrical condensate evaporation integrated as standard (from 3412.14 BTU/h), protection class UL Type 3R/4, 12.



Features

Model No.	SK 3304.518
Version	wall-mounted
Product description	Energy-efficient Blue e wall-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard. Protection category UL Type 3R/4, 12.
Benefits	Suitable for outdoor installation Blue e technology May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers
Material	Carbon steel
Color	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Wired ready for connection (plug-in terminal strip) Drilling template Fasteners Integral electric condensate evaporation

Features

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 1.1 kW Cooling output L35 L35/60 Hz: 1.25 kW Cooling output L35 L50/50 Hz: 0.91 kW Cooling output L35 L50/60 Hz: 0.9 kW Cooling output L35 L35/50 Hz: 3,753 BTU/h Cooling output L35 L35/60 Hz: 4,265 BTU/h Cooling output L35 L50/50 Hz: 3,105 BTU/h Cooling output L35 L50/60 Hz: 3,071 BTU/h
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 8.7 A At 60 Hz: 9.7 A
Start-up current (max.)	At 50 Hz: 26 A At 60 Hz: 28 A
Air throughput (unimpeded air flow)	External circuit: 805 m ³ /h Internal circuit: 600 m ³ /h External circuit: 473.8 cfm Internal circuit: 353.1 cfm
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.67 Refrigeration factor L35 L35 (EER) 60 Hz: 1.52
Version	wall-mounted
Dimensions	Width: 405 mm Height: 1,020 mm Depth: 358 mm Width: 15.9 " Height: 40.2 " Depth: 14.1 "
Protection category IP to EN 60529	External circuit, IP 34 Internal circuit IP 56
Protection category NEMA	UL Type 3R UL Type 4 UL Type 12

Features

Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.325 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.21 t Refrigerant: R-513A Quantity: 0.7 lb.
Temperature control	e-Comfort Controller (factory setting +35 °C)
Operating temperature range	-20 °C...50 °C -4 °F...122 °F
Operating temperature	Compressor cooling mode from +10 °C ambient temperature. Only the internal fan is active in the temperature range -20 °C to +10 °C.
Storage temperature range	-40 °C...70 °C -40 °F...158 °F
Setting range	20 °C...50 °C 68 °F...122 °F
Rated power Pel	Rated power L35 L35/50 Hz: 0.66 kW Rated power L35 L35/60 Hz: 0.82 kW Rated power L35 L50/50 Hz: 0.77 kW Rated power L35 L50/60 Hz: 0.89 kW
Permissible operating pressure (p. max.)	28 bar 406.1 PSI
Pre-fuse	Transformer circuit-breaker: 11...16 A
Packaging unit	1 pc(s).
Net weight	70 kg
Gross weight	75 kg
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK cooling unit Blue e, wall-mounted, 3753 BTU/h 115 V, 1~, 50/60 Hz, carbon steel, WHD: 405 x 1020 x 358 mm

Approvals

Approvals

UL + C-UL (listed)

UL + C-UL - FTTA

Explanations

Declaration of conformity

Declaration of conformity - F-gas regulation

Declaration of conformity UK