Rittal – The System.

Faster – better – everywhere.





SK 3241.600 TopTherm Filter Fan Units

State: 11/6/2025 (Source: rittal.com/us-en)



SK 3241.600 - TopTherm Filter Fan Units EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 11.77 - 529.72 cfm, protection category IP 54 as standard.





Features

Model No.	SK 3241.600
Version	wall-mounted EMC
Product description	EMC fan-and-filter units have a high screening/dampening effect and meet performance level 2 as per EN 61587-3.
Product modification	Since May 2024, the cover for the connection terminal is no longer part of the TopTherm filter fan. During testing, it was found not to be required by the standards and does not impair function or operational safety.
Color	RAL 7035
Supply includes	Complete unit ready to install, including chopped fiber filter mat
Fan	Diagonal, shaded pole motor
Air throughput (unimpeded air	At 50 Hz: 225 m³/h
flow)	At 60 Hz: 245 m³/h
	At 50 Hz: 132.4 cfm
	At 60 Hz: 144.2 cfm
Air throughput with outlet filter	1 x 3240060: 171/182 m³/h
incl. chopped fiber filter mat (quantity x order number)	2 x 3240060: 200/217 m³/h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz

© Rittal 2025 2

Features

Rated current max.	At 50 Hz: 0.26 A At 60 Hz: 0.24 A
Rated power Pel	At 50 Hz: 40 W
	At 60 Hz: 42 W
Dimensions	Width: 255 mm
	Height: 255 mm
	Width: 10 "
	Height: 10 "
Installation dimensions	Build depth: 25 mm
	Installation depth: 107 mm
	Build depth: 0.98 "
	Installation depth: 4.21 ″
Mounting cut-out	Width of opening: 224 mm
Woulding out out	Cut-out height: 224 mm
	Width of opening: 8.82 "
	Cut-out height: 8.82 "
	Out out neight. 0.02
Note	To improve energy efficiency and increase equipment service life,
	we recommend thermostats or temperature displays.
Protection category IP to IEC 60	IP 54 with fleece filter
529	IP 56 with fleece filter and hose-proof hood
Protection category NEMA	Type 12 with fleece filter
	Type 3
	Type 3R
	Type 4
	1,700 1
	Type 4X with fleece filter and hose-proof hood
Pre-fuse	
Pre-fuse Service life of fans (L10, 40 °C))	Type 4X with fleece filter and hose-proof hood
	Type 4X with fleece filter and hose-proof hood Miniature circuit-breaker/fuse: 4 A
	Type 4X with fleece filter and hose-proof hood Miniature circuit-breaker/fuse: 4 A At 50 Hz: 61,000 h
Service life of fans (L10, 40 °C))	Type 4X with fleece filter and hose-proof hood Miniature circuit-breaker/fuse: 4 A At 50 Hz: 61,000 h At 60 Hz: 60,000 h
Service life of fans (L10, 40 °C)) Operating temperature range	Type 4X with fleece filter and hose-proof hood Miniature circuit-breaker/fuse: 4 A At 50 Hz: 61,000 h At 60 Hz: 60,000 h -30 °C55 °C -22 °F131 °F
Service life of fans (L10, 40 °C))	Type 4X with fleece filter and hose-proof hood Miniature circuit-breaker/fuse: 4 A At 50 Hz: 61,000 h At 60 Hz: 60,000 h -30 °C55 °C
Service life of fans (L10, 40 °C)) Operating temperature range	Type 4X with fleece filter and hose-proof hood Miniature circuit-breaker/fuse: 4 A At 50 Hz: 61,000 h At 60 Hz: 60,000 h -30 °C55 °C -22 °F131 °F -30 °C70 °C

© Rittal 2025 3

Features

Packaging unit	1 pc(s).
Net weight	2.1
Gross weight	2.275
Customs tariff number	84145915
EAN	4028177652460
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025