

Rittal – The System.

Faster – better – everywhere.



SK 3311.011 Fan module

State: 12/14/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3311.011 - Fan module For LCP rack/Inline, CW

For increased cooling output. Also redundancy can be achieved or the electrical power consumption can be reduced .



Features

Model No.	SK 3311.011
Product description	To increase the cooling output, individual fan modules can be retro-fitted into the LCPs. Similarly, additional integration makes it possible to generate redundancy or reduce the electrical power consumption of the LCP.
Benefits	Can be connected during operation Tool-free fan module replacement
Function principle	Installation of fan modules in an LCP increases the air performance, and thus, the cooling capacity of the respective variant. If cooling capacity is sufficient, the addition of fan modules can be used to form redundancies. Retrofitting fans in excess of the required air flow can reduce electrical energy consumption, as fans will then operate at a lower speed. The noise level of the device is also significantly reduced.
Color	RAL 9005
Supply includes	1 fan unit EC fan Wired ready for connection Assembly components

Features

Note	<p>The LCP SK 3311.130/.230/.530 (max. 30 kW) is supplied with one fan module as standard.</p> <p>To achieve the max. cooling output of 30 kW, the customer/service should install two additional fan modules.</p> <p>The LCP SK 3311.260/.560/.530 (max. 55 kW) is supplied with four fan modules as standard.</p> <p>To achieve the max. cooling output of 55 kW, the customer/service should install two additional fan modules.</p> <p>The LCP 3311.540 (max. 30 kW) is supplied with two fan modules as standard.</p> <p>To achieve the max. cooling output of 30 kW, the customer/service should install two additional fan modules.</p>
Packaging unit	1 pc(s).
Net weight	6.851
Gross weight	7.212
Customs tariff number	84145915
EAN	4028177688117
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---