## Rittal – The System.

Faster – better – everywhere.





# SK 3311.360 Condenser Unit

State: 11/29/2025 (Source: rittal.com/us-en)



#### SK 3311.360 - Condenser Unit For LCP DX

The condenser units are needed for operating refrigerant-based LCPs. Depending on the version, the units have an external condenser and ventilator or an additional free cooler. The version with the free cooler is required for the LCP DX/FC combination version. The units are suitable for roof or wall mounting.

#### **Features**

|   | Model No.                  | SK 3311.360  |
|---|----------------------------|--|
| and comprises the external condenser and two fans that are speed controlled by means of pressure in the cooling circuit.  Material Carbon steel, spray finished  Surface finish Powder-coated, galvanized  Color RAL 9003  Supply includes  Assembly parts  Max. cooling output 12 kW 40,946 BTU/h  Temperature control Speed-Controlled Fan  Refrigerant/cooling medium Refrigerant: R410A Cooling medium: -  Dimensions Width: 1,303 mm Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan modules | Version                    | Condensers   |
| Surface finish Powder-coated, galvanized  Color RAL 9003  Supply includes Assembly parts  Max. cooling output 12 kW 40,946 BTU/h  Temperature control Speed-Controlled Fan  Refrigerant/cooling medium Refrigerant: R410A Cooling medium: -  Dimensions Width: 1,303 mm Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan modules   | Product description        | The condenser unit is needed to operate the refrigerant-based LCPs, and comprises the external condenser and two fans that are speed-controlled by means of pressure in the cooling circuit. |
| Color  RAL 9003  Supply includes  Assembly parts  Max. cooling output  12 kW 40,946 BTU/h  Temperature control  Speed-Controlled Fan  Refrigerant/cooling medium  Refrigerant: R410A Cooling medium: -  Dimensions  Width: 1,303 mm Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan modules   | Material                   | Carbon steel, spray finished   |
| Supply includes  Assembly parts  Max. cooling output  12 kW 40,946 BTU/h  Temperature control  Speed-Controlled Fan  Refrigerant/cooling medium  Refrigerant: R410A Cooling medium: -  Dimensions  Width: 1,303 mm Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan modules  | Surface finish             | Powder-coated, galvanized  |
| Assembly parts  Max. cooling output  12 kW 40,946 BTU/h  Temperature control  Speed-Controlled Fan  Refrigerant/cooling medium  Refrigerant: R410A Cooling medium: -  Dimensions  Width: 1,303 mm Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan modules   | Color                      | RAL 9003   |
| Max. cooling output  12 kW 40,946 BTU/h  Temperature control  Speed-Controlled Fan  Refrigerant/cooling medium  Refrigerant: R410A Cooling medium: -  Dimensions  Width: 1,303 mm Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan modules   | Supply includes            |  |
| 40,946 BTU/h  Temperature control Speed-Controlled Fan  Refrigerant/cooling medium Refrigerant: R410A Cooling medium: -  Dimensions Width: 1,303 mm Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan modules   |                            | Assembly parts   |
| Temperature control  Refrigerant/cooling medium  Refrigerant: R410A Cooling medium: -  Dimensions  Width: 1,303 mm Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan modules  | Max. cooling output        | 12 kW  |
| Refrigerant/cooling medium Refrigerant: R410A Cooling medium: -  Width: 1,303 mm Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan amodules  Total cooling output/number of fan amodules  |                            | 40,946 BTU/h   |
| Cooling medium: -  Width: 1,303 mm Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan amodules   | Temperature control        | Speed-Controlled Fan   |
| Dimensions  Width: 1,303 mm  Height: 915 mm  Depth: 620 mm  Width: 51.3 "  Height: 36 "  Depth: 24.4 "  Total cooling output/number of fan modules  Total cooling output/number of fan modules  | Refrigerant/cooling medium | Refrigerant: R410A   |
| Height: 915 mm Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan 2 modules   |                            | Cooling medium: -  |
| Depth: 620 mm Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan 2 modules  | Dimensions                 | Width: 1,303 mm  |
| Width: 51.3 " Height: 36 " Depth: 24.4 "  Total cooling output/number of fan 2 modules  |                            | Height: 915 mm   |
| Height: 36 ″ Depth: 24.4 ″  Total cooling output/number of fan 2 modules  |                            | Depth: 620 mm  |
| Depth: 24.4 "  Total cooling output/number of fan 2 modules   |                            | Width: 51.3 "  |
| Total cooling output/number of fan 2 modules  |                            |  |
| modules   |                            | Depth: 24.4 "  |
| Rated operating voltage 230 V, 1~, 50 Hz/60 Hz  |                            | 2  |
|   | Rated operating voltage    | 230 V, 1~, 50 Hz/60 Hz   |

© Rittal 2025 2

### Features

| Packaging unit        | 1 pc(s).      |
|-----------------------|---------------|
| Net weight            | 50            |
| Gross weight          | 50            |
| Customs tariff number | 84189910      |
| EAN                   | 4028177691438 |
| ETIM 9                | EC002515      |
| ETIM 8                | EC002515      |
| ECLASS 8.0            | 27180712      |

## **Approvals**

| Otift        | F40 |  |
|--------------|-----|--|
| Certificates | EAC |  |

© Rittal 2025 3