

# Rittal – The System.

Faster – better – everywhere.



## SK 3320.600 TopTherm chillers

State: 5/13/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3320.600 - TopTherm chillers 3412.1 - 13,648 BTU/h

TopTherm chillers in roof-mounted or stand-alone versions are flexible and compact. They offer centralized and efficient cooling of the cooling water and supply air/water heat exchangers and other devices. With nano-coated condenser as standard.

## Features

Model No.	SK 3320.600
Version	Compact, modular layout of the refrigeration components Pump to convey the medium
Benefits	Precise temperature control, based on microprocessor technology Collective fault signal with floating contact One version for two frequencies = international compatibility
Color	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Complete unit ready for connection Multilingual documentation including functional diagram and wiring plans
Protection category IP to EN 60 529	IP 44 (electrics)
Total cooling output Tw10 / Tu32	Cooling output Tw10 Tu32/50 Hz: 2.7 kW Cooling output Tw10 Tu32/60 Hz: 3 kW Cooling output Tw10 Tu32/50 Hz: 9,213 BTU/h Cooling output Tw10 Tu32/60 Hz: 10,236 BTU/h
Total cooling output Tw18 / Tu32	Cooling output Tw18 Tu32/50 Hz: 3 kW Cooling output Tw18 Tu32/60 Hz: 3.4 kW Cooling output Tw18 Tu32/50 Hz: 10,236 BTU/h Cooling output Tw18 Tu32/60 Hz: 11,601 BTU/h
Total cooling output to DIN EN 14511 Tw18 / Tu35	Cooling output Tw18 Tu35/50 Hz: 2.6 kW Cooling output Tw18 Tu35/60 Hz: 3.3 kW
Air throughput (unimpeded air flow)	At 50 Hz: 1,785 m <sup>3</sup> /h At 60 Hz: 1,785 m <sup>3</sup> /h At 50 Hz: 1,050.6 cfm At 60 Hz: 1,050.6 cfm

# Features

Rated operating voltage	400 V, 3~, 50 Hz 460 V, 3~, 60 Hz
Dimensions	Width: 602 mm Height: 676 mm Depth: 645 mm Width: 23.7 " Height: 26.6 " Depth: 25.4 "
Temperature control	Microcontroller control (factory setting +20 °C)
Operating temperature range	10 °C...43 °C 50 °F...109 °F
Operating temperature range of cooling medium	10 °C: 30 °C 50 °F: 86 °F
Temperature hysteresis	± 2 K
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 1.2 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.75 t Refrigerant: R-513A Quantity: 2.6 lb.
Volumetric flow (cooling medium)	At 50 Hz: 20 l/min
Rated power Pel	At 50 Hz: 2.03 kW At 60 Hz: 2.67 kW
Rated current max.	At 50 Hz: 4.05 A At 60 Hz: 4.35 A
Refrigeration factor (EER) 50 Hz Tw18 / Tu35 DIN EN 14511	2.53
Water circuit	Open
Water connections	G ½" internal thread
Number of cooling circuits	1
Tank	Material: Plastic PP Volume: 30 l
Packaging unit	1 pc(s).

# Features

---

Net weight	88 kg
Gross weight	98 kg
Customs tariff number	84186900
ETIM 9	EC002516
ETIM 8	EC002516
ECLASS 8.0	27180713
Product description	SK Chiller TopTherm, Stand alone, open, 8872/11260 BTU/h, 400-460 V, 3~, 50/60 Hz, WHD: 602 x 676 x 645 mm

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity - F-gas regulation
--------------	---