

# Rittal – The System.

Faster – better – everywhere.



## SK 3329.514

# TopTherm Blue e Wall-Mounted Cooling Unit, NEMA 4X

State: 6/19/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3329.514 - TopTherm Blue e Wall-Mounted Cooling Unit, NEMA 4X 1706.07 - 8530.36 BTU/h

Energy-efficient Blue e wall-mounted cooling units in power categories 1706.07 - 8530.36 BTU/h with e-Comfort controller integrated as standard and electrical condensate evaporation. Protection category NEMA 4X.



## Features

|                     |  |
|---------------------|--|
| Model No.           | SK 3329.514  |
| Version             | wall-mounted   |
| Product description | Energy-efficient Blue e wall-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard. Protection category NEMA 4X.            |
| Benefits            | May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers                                    |
| Material            | Stainless steel 1.4404 (AISI 316L)   |
| Color               | RAL 7001   |
| Supply includes     | Condenser with hydrophobic RiNano coating<br>Wired ready for connection (plug-in terminal strip)<br>Drilling template<br>Fasteners<br>Integral electric condensate evaporation |

# Features

|  |   |
|--|---|
| Total cooling output to DIN EN 14511           | Cooling output L35 L35/50 Hz: 2.55 kW<br>Cooling output L35 L35/60 Hz: 2.6 kW<br>Cooling output L35 L50/50 Hz: 1.8 kW<br>Cooling output L35 L50/60 Hz: 1.8 kW<br>Cooling output L35 L35/50 Hz: 8,701 BTU/h<br>Cooling output L35 L35/60 Hz: 8,872 BTU/h<br>Cooling output L35 L50/50 Hz: 6,142 BTU/h<br>Cooling output L35 L50/60 Hz: 6,142 BTU/h |
| Rated operating voltage                        | 115 V, 1~, 50 Hz/60 Hz  |
| Rated current max.                             | At 50 Hz: 17 A<br>At 60 Hz: 22 A  |
| Start-up current (max.)                        | At 50 Hz: 44 A<br>At 60 Hz: 42 A  |
| Air throughput (unimpeded air flow)            | External circuit: 710 m <sup>3</sup> /h<br>Internal circuit: 640 m <sup>3</sup> /h<br>External circuit: 417.9 cfm<br>Internal circuit: 376.7 cfm  |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 2.11<br>Refrigeration factor L35 L35 (EER) 60 Hz: 1.7   |
| Version  | wall-mounted  |
| Dimensions                                     | Width: 405 mm<br>Height: 1,650 mm<br>Depth: 388 mm<br>Width: 15.9 "<br>Height: 65 "<br>Depth: 15.3 "  |
| Protection category IP to EN 60 529            | External circuit, IP 34<br>Internal circuit IP 55   |
| Protection category NEMA                       | NEMA 4X   |
| Refrigerant/cooling medium                     | Refrigerant: R-513A<br>Quantity: 1.1 kg<br>Global Warming Potential (GWP): 631<br>CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 0.69 t<br>Refrigerant: R-513A<br>Quantity: 2.4 lb.  |

# Features

|  |   |
|--|---|
| Temperature control                      | e-Comfort Controller (factory setting +35 °C)   |
| Operating temperature range              | 10 °C...50 °C<br>50 °F...122 °F   |
| Storage temperature range                | -40 °C...70 °C<br>-40 °F...158 °F   |
| Setting range                            | 20 °C...50 °C<br>68 °F...122 °F   |
| Rated power Pel                          | Rated power L35 L35/50 Hz: 1.21 kW<br>Rated power L35 L35/60 Hz: 1.53 kW<br>Rated power L35 L50/50 Hz: 1.41 kW<br>Rated power L35 L50/60 Hz: 1.8 kW |
| Permissible operating pressure (p. max.) | 28 bar<br>406.1 PSI   |
| Pre-fuse                                 | Transformer circuit-breaker: 18...25 A  |
| Packaging unit                           | 1 pc(s).  |
| Net weight                               | 75.4 kg   |
| Gross weight                             | 108 kg  |
| Customs tariff number                    | 84158200  |
| ETIM 9                                   | EC000855  |
| ETIM 8                                   | EC000855  |
| ECLASS 8.0                               | 27180704  |
| Product description                      | SK cooling unit Blue e, wall-mounted, 8701 BTU/h, 115 V, 1~, 50/60 Hz, stainless steel, WHD: 405 x 1650 x 388 mm                                    |

# Approvals

|           |  |
|-----------|--|
| Approvals | UL + C-UL (listed)<br>UL + C-UL - FTTA<br>UR + C-UR (recognized) |
|-----------|--|

# Approvals

---

Explanations

FCC

Declaration of conformity

Declaration of conformity - F-gas regulation

Declaration of conformity UK