

Rittal – The System.

Faster – better – everywhere.



SK 3245.810 Blue e+ filter fan

State: 5/4/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3245.810 - Blue e+ filter fan EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 11.77 - 529.72 cfm, protection category IP 54 as standard.



Features

Model No.	SK 3245.810
Version	wall-mounted EMC
Product description	EMC fan-and-filter units have a high screening/dampening effect and meet performance level 2 as per EN 61587-3.
Benefits	Easy filter change thanks to a new opening mechanism on the louvre grille Faster assembly on the enclosure due to optimized snap hooks Diagonal fan technology ensures more uniform and consistent ventilation of the control cabinet through higher pressure stability. Tool-free mounting
Material	Plastic
Color	RAL 7035
Supply includes	Complete unit ready to install, including EMC filter mat
Fan	Diagonal, EC motor
Unimpeded air flow (with fleece filter)	At 50 Hz: 931 m ³ /h At 50 Hz: 548 cfm

Features

Airflow with corresponding outlet filter including fleece filter	At 50 Hz: 728 m ³ /h At 50 Hz: 428.48 cfm
Rated operating voltage	100 V - 130 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 174.6 W
Rated current max.	At 50 Hz: 2.52 A
Dimensions	Width: 323 mm Height: 323 mm Depth: 156 mm Width: 12.7 " Height: 12.7 " Depth: 6.14 "
Installation depth	136 mm 5.35 "
Mounting cut-out	Width of opening: 292 mm Cut-out height: 292 mm Width of opening: 11.5 " Cut-out height: 11.5 "
Protection category IP to IEC 60529	IP51 with fleece filter IP56 with fleece filter and hose-proof hood
Protection category NEMA	Type 12 with fleece filter Type 3, 3R with fleece filter and hose-proof hood
Note	To improve energy efficiency and increase equipment service life, we recommend thermostats or temperature displays.
Operating temperature range	-25 °C...55 °C -13 °F...131 °F
Storage temperature range	-25 °C...70 °C -13 °F...158 °F
Noise pressure level	At 50 Hz: 72 dB(A)
Interfaces	0 - 10 V/PWM input Speed output
Packaging unit	1 pc(s).
Net weight	3.2

Features

Customs tariff number	84145915
EAN	4028177997820
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity
