Rittal - The System.

Faster – better – everywhere.





SK 3301.392 Air Duct

State: 10/27/2025 (Source: rittal.com/us-en)



SK 3301.392 - Air Duct For lateral air routing

For the supply of cold air to switches with lateral air intake.

Features

Model No.	SK 3301.392
Product description	Air duct, passive, for cold air intake to 19" IT equipment with side air inlet. Suitable for use in conjunction with all-round partitioning around the mounting level via air baffle plates and targeted management of the airflow through the air duct.
Benefits	To improve air supply to 19" IT equipment with lateral air routing Integral membrane cover allows cable entry to the rear depth-variable
Material	Carbon steel
Surface finish	Spray-finished
Color	RAL 9005
Supply includes	Air Duct Adapter for fastening to 19" profile rails Magnetic strip for covering the remaining vertical openings in the air baffle plate
Installation options	for TS IT 19" profile rails for TS IT 19" mounting frames for 19" standard profile rails
Mounting tip	Can only be fitted to the front 19" installation level Can only be mounted in the area of the vertical 19" openings in the air baffle
Dimensions	Height: 2 U
Suitable for	Enclosure type: TS IT VX IT Width: 800 mm Enclosure type: TS IT VX IT Width: 31.5 "

© Rittal 2025

Features

Packaging unit	1 pc(s).
Net weight	1.55
Gross weight	1.8
PCF/VE (cradle-to-gate)	6.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177716612
ETIM 9	EC011217
ETIM 8	EC011217
ECLASS 8.0	22410601

© Rittal 2025 3