

Rittal – The System.

Faster – better – everywhere.



SK 3355.720

Electrical Condensate Evaporators

State: 1/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3355.720 - Electrical Condensate Evaporators for roof-mounted Blue e+ cooling units

Condensate evaporation helps to evaporate any condensation and emit it to the ambient air via the air exhaust of the cooling unit.



Features

Model No.	SK 3355.720
Product description	The condensate evaporator can be mounted tool-free on the underside of the roof-mounted Blue e+ cooling unit so it is not visible from the outside. Any condensation is evaporated and emitted to the ambient air via the air exhaust of the cooling unit.
Material	Plastic
Color	RAL 9005
Supply includes	Electrical Condensate Evaporators Transport clamp screw Grommet
Evaporation performance	100 ml/h
Note	Power is supplied by the cooling unit
Suitable for Model No.	3185.730
Dimensions	Width: 89 mm Height: 121 mm Depth: 158 mm Width: 3.5 “ Height: 4.76 “ Depth: 6.22 “

Features

Operating temperature range	5 °C...60 °C 41 °F...140 °F
Rated operating voltage	380 V (DC)
Packaging unit	1 pc(s).
Net weight	0.4
Gross weight	0.5
Customs tariff number	84189910
EAN	4028177931787
ETIM 9	EC002009
ETIM 8	EC002009
ECLASS 8.0	27180715

Approvals

Certificates	EAC
--------------	-----