

# Rittal – The System.

Faster – better – everywhere.



## SK 3305.500

# Wall-Mounted Cooling Unit TopTherm Blue e

State: 5/21/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3305.500 - Wall-Mounted Cooling Unit TopTherm Blue e 1023.64 - 13,648.6 BTU/h

Energy efficient Blue e wall mounting cooling units in performance classes 1023.64 to 13648.57 BTU/h, and with integrated electrical condensation evaporation for 3412.14 BTU/h and above. Available in the special formats "horizontal" and "flat".

## Features

|                                      |   |
|--------------------------------------|---|
| Model No.                            | SK 3305.500   |
| Version                              | wall-mounted  |
| Product description                  | Energy efficient Blue e wall-mounted cooling units in performance classes 300 W to 4000 W and with integrated electrical condensation evaporation for 1000 W and above.   |
| Benefits                             | May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers   |
| Material                             | Carbon steel  |
| Color                                | RAL 7035  |
| Supply includes                      | Condenser with hydrophobic RiNano coating<br>Wired ready for connection (plug-in terminal strip)<br>Drilling template<br>Fasteners<br>Integral electric condensate evaporation  |
| Total cooling output to DIN EN 14511 | Cooling output L35 L35/50 Hz: 1.6 kW<br>Cooling output L35 L35/60 Hz: 1.73 kW<br>Cooling output L35 L50/50 Hz: 1.18 kW<br>Cooling output L35 L50/60 Hz: 1.26 kW<br>Cooling output L35 L35/50 Hz: 5,459 BTU/h<br>Cooling output L35 L35/60 Hz: 5,903 BTU/h<br>Cooling output L35 L50/50 Hz: 4,026 BTU/h<br>Cooling output L35 L50/60 Hz: 4,299 BTU/h |
| Rated operating voltage              | 230 V, 1~, 50 Hz/60 Hz  |

# Features

|  |   |
|--|---|
| Rated current max.                             | At 50 Hz: 6.1 A<br>At 60 Hz: 6.5 A  |
| Start-up current (max.)                        | At 50 Hz: 12 A<br>At 60 Hz: 14 A  |
| Air throughput (unimpeded air flow)            | External circuit: 805 m <sup>3</sup> /h<br>Internal circuit: 585 m <sup>3</sup> /h<br>External circuit: 473.8 cfm<br>Internal circuit: 344.3 cfm                                      |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 1.83<br>Refrigeration factor L35 L35 (EER) 60 Hz: 1.79  |
| Version  | wall-mounted  |
| Dimensions                                     | Width: 400 mm<br>Height: 950 mm<br>Depth: 260 mm<br>Width: 15.7 "<br>Height: 37.4 "<br>Depth: 10.2 "  |
| Protection category IP to EN 60529             | External circuit, IP 34<br>Internal circuit, IP 54  |
| Protection category NEMA                       | UL Type 12  |
| Refrigerant/cooling medium                     | Refrigerant: R-513A<br>Quantity: 0.61 kg<br>Global Warming Potential (GWP): 631<br>CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 0.38 t<br>Refrigerant: R-513A<br>Quantity: 1.3 lb. |
| Temperature control                            | e-Comfort Controller (factory setting +35 °C)   |
| Operating temperature range                    | 10 °C...55 °C<br>50 °F...131 °F   |
| Storage temperature range                      | -40 °C...70 °C<br>-40 °F...158 °F   |
| Setting range                                  | 20 °C...55 °C<br>68 °F...131 °F   |

# Features

---

|  |   |
|--|---|
| Rated power Pel                          | Rated power L35 L35/50 Hz: 0.87 kW<br>Rated power L35 L35/60 Hz: 0.96 kW<br>Rated power L35 L50/50 Hz: 0.91 kW<br>Rated power L35 L50/60 Hz: 1 kW |
| Permissible operating pressure (p. max.) | 28 bar<br>406.1 PSI   |
| Pre-fuse                                 | Miniature circuit-breaker/fuse: 16 A  |
| Packaging unit                           | 1 pc(s).  |
| Net weight                               | 39.75 kg  |
| Gross weight                             | 42 kg   |
| Customs tariff number                    | 84158200  |
| ETIM 9                                   | EC000855  |
| ETIM 8                                   | EC000855  |
| ECLASS 8.0                               | 27180704  |
| Product description                      | SK cooling unit Blue e, wall-mounted, 5459 BTU/h 230 V, 1~, 50/60 Hz, carbon steel, WHD: 400 x 950 x 260 mm                                       |

---

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | 30 - KC Korea<br>UL + C-UL (listed)<br>UL + C-UL - FTTA   |
| Explanations | Declaration of conformity<br>Declaration of conformity - F-gas regulation<br>Declaration of conformity UK |

---