Rittal – The System.

Faster – better – everywhere.



SK 3311.040

Connection hose

State: 11/9/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3311.040 - Connection hose

Flexible connection hose, may be shortened, including union nuts on both sides for connecting the LCP/LCU to existing pipework.

Features

Model No.	SK 3311.040
Material	NBR (inner) with steel spiral and fabric insert
Version	Rack cooling
Length	1.8 m 70.9 ″
Water connections	G 1½" internal thread
Operating temperature range	-30 °C...70 °C -22 °F...158 °F
Permissible operating pressure (p. max.)	16 bar 232.1 PSI
Packaging unit	2 pc(s).
Net weight	6.302 kg
Gross weight	6.779 kg
Customs tariff number	39173200
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	SK connection hose, for water connection below and above, for LCP Rack/Inline CW, L: 1800 mm

© Rittal 2026