
## Rittal – The System.

Faster – better – everywhere.





# SK 3311.363 Condenser Unit

State: 10/30/2025 (Source: rittal.com/us-en)



#### SK 3311.363 - Condenser Unit For LCP DX

The condenser units are needed for operating refrigerant-based LCPs. Depending on the version, the units have an external condenser and ventilator or an additional free cooler. The version with the free cooler is required for the LCP DX/FC combination version. The units are suitable for roof or wall mounting.

#### **Features**

Model No.	SK 3311.363
Version	Condensers
Product description	The condenser unit is needed to operate the refrigerant-based LCPs, and comprises the external condenser and two fans that are speed-controlled by means of pressure in the cooling circuit.
Material	Carbon steel, spray finished
Surface finish	Powder-coated, galvanized
Color	RAL 9003
Supply includes	Assembly parts
Max. cooling output	20 kW 68,243 BTU/h
Temperature control	Speed-Controlled Fan
Refrigerant/cooling medium	Refrigerant: R410A Cooling medium: -
Dimensions	Width: 2,282 mm  Height: 480 mm  Depth: 508 mm  Width: 89.8 "  Height: 18.9 "  Depth: 20 "
Total cooling output/number of fan modules	3
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz

© Rittal 2025

### Features

Packaging unit	1 pc(s).
Net weight	65
Gross weight	113
Customs tariff number	84189910
EAN	4028177716643
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

## **Approvals**

|--|

© Rittal 2025 3