

**Rittal – The System.**

Faster – better – everywhere.



**SK 3385.540**

# TopTherm Blue e Roof-Mounted Cooling Unit

State: 4/12/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3385.540 - TopTherm Blue e Roof-Mounted Cooling Unit Total cooling output 1706.07 - 13648.57 BTU/h

Energy-efficient Blue e roof-mounted cooling units in output categories 1706.07 - 13648.57 BTU/h with e-Comfort controller integrated as standard and electrical condensate evaporation.



## Features

Model No.	SK 3385.540
Version	roof-mounted
Product description	Energy-efficient Blue e roof-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard.
Benefits	May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers
Material	Carbon steel
Color	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Integral electric condensate evaporation Wired ready for connection (plug-in terminal strip) Drilling template Fasteners

# Features

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 2 kW Cooling output L35 L35/60 Hz: 2.14 kW Cooling output L35 L50/50 Hz: 1.58 kW Cooling output L35 L50/60 Hz: 1.51 kW Cooling output L35 L35/50 Hz: 6,824 BTU/h Cooling output L35 L35/60 Hz: 7,302 BTU/h Cooling output L35 L50/50 Hz: 5,391 BTU/h Cooling output L35 L50/60 Hz: 5,152 BTU/h
Rated operating voltage	400 V, 2~, 50 Hz/60 Hz
Note	Due to its low noise level, the roof-mounted cooling unit 3273.500 is also suitable for use in office applications.
Rated current max.	At 50 Hz: 4.2 A At 60 Hz: 4.4 A
Start-up current (max.)	At 50 Hz: 11.7 A At 60 Hz: 11.7 A
Air throughput (unimpeded air flow)	External circuit: 1,760 m <sup>3</sup> /h Internal circuit: 470 m <sup>3</sup> /h External circuit: 1,035.9 cfm Internal circuit: 276.6 cfm
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.96 Refrigeration factor L35 L35 (EER) 60 Hz: 1.69
Version	roof-mounted
Dimensions	Width: 597 mm Height: 417 mm Depth: 475 mm Width: 23.5 " Height: 16.4 " Depth: 18.7 "
Protection category IP to EN 60 529	External circuit, IP 34 Internal circuit, IP 54
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.9 kg Global Warming Potential (GWP): 631 CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 0.57 t Refrigerant: R-513A Quantity: 2 lb.

# Features

Type of connection (electrical)	Plug-in terminal strip
Duty cycle	100 %
Temperature control	e-Comfort Controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C 50 °F...131 °F
Operating temperature max @60 Hz	53 °C 127 °F
Storage temperature range	-40 °C...70 °C -40 °F...158 °F
Setting range	20 °C...53 °C 68 °F...127 °F
Rated power Pel	Rated power L35 L35/50 Hz: 1.02 kW Rated power L35 L35/60 Hz: 1.27 kW Rated power L35 L50/50 Hz: 1.15 kW Rated power L35 L50/60 Hz: 1.29 kW
Permissible operating pressure (p. max.)	28 bar 406.1 PSI
Pre-fuse	Transformer circuit-breaker: 6.3...10 A
Packaging unit	1 pc(s).
Net weight	58.9 kg
Gross weight	62 kg
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK cooling unit Blue e, roof-mounted, 6824 BTU/h, 400 V, 2~, 50/60 Hz, carbon steel, WHD: 597 x 417 x 475 mm

# Approvals

---

Approvals

UL + C-UL (listed)

UL + C-UL - FTTA

---

Explanations

Declaration of conformity

Declaration of conformity - F-gas regulation

Declaration of conformity UK