Rittal – The System.

Faster – better – everywhere.



# SK 3387.540

# TopTherm Blue e Roof-Mounted Cooling Unit

State: 11/12/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SK 3387.540 - TopTherm Blue e Roof-Mounted Cooling Unit Total cooling output 1706.07 - 13648.57 BTU/h

Energy-efficient Blue e roof-mounted cooling units in output categories 1706.07 - 13648.57 BTU/h with e-Comfort controller integrated as standard and electrical condensate evaporation.

## Features

| | |
|---|---|
| Model No. | SK 3387.540 |
| Version | roof-mounted |
| Product description | Energy-efficient Blue e roof-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard. |
| Benefits | May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers |
| Material | Carbon steel |
| Color | RAL 7035 |
| Supply includes | Condenser with hydrophobic RiNano coating<br>Integral electric condensate evaporation<br>Wired ready for connection (plug-in terminal strip)<br>Drilling template<br>Fasteners |
| Total cooling output to DIN EN 14511 | Cooling output L35 L35/50 Hz: 3.8 kW<br>Cooling output L35 L35/60 Hz: 4 kW<br>Cooling output L35 L50/50 Hz: 3.05 kW<br>Cooling output L35 L50/60 Hz: 3.3 kW<br>Cooling output L35 L35/50 Hz: 12,966 BTU/h<br>Cooling output L35 L35/60 Hz: 13,649 BTU/h<br>Cooling output L35 L50/50 Hz: 10,407 BTU/h<br>Cooling output L35 L50/60 Hz: 11,260 BTU/h |
| Rated operating voltage | 400 V, 3~, 50 Hz<br>460 V, 3~, 60 Hz |

© Rittal 2026

# Features

| | |
|---|---|
| Note | Due to its low noise level, the roof-mounted cooling unit 3273.500 is also suitable for use in office applications. |
| Rated current max. | At 50 Hz: 4.1 A<br>At 60 Hz: 4.5 A |
| Start-up current (max.) | At 50 Hz: 17 A<br>At 60 Hz: 19 A |
| Air throughput (unimpeded air flow) | External circuit: 3,870 m³/h<br>Internal circuit: 1,420 m³/h<br>External circuit: 2,277.8 cfm<br>Internal circuit: 835.8 cfm |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 2.24<br>Refrigeration factor L35 L35 (EER) 60 Hz: 1.97 |
| Version | roof-mounted |
| Dimensions | Width: 796 mm<br>Height: 470 mm<br>Depth: 580 mm<br>Width: 31.3 ″<br>Height: 18.5 ″<br>Depth: 22.8 ″ |
| Protection category IP to EN 60 529 | External circuit, IP 34<br>Internal circuit, IP 54 |
| Refrigerant/cooling medium | Refrigerant: R-513A<br>Quantity: 1.8 kg<br>Global Warming Potential (GWP): 631<br>CO2 equivalent (CO2e): 1.14 t<br>Refrigerant: R-513A<br>Quantity: 4 lb. |
| Type of connection (electrical) | Plug-in terminal strip |
| Duty cycle | 100 % |
| Temperature control | e-Comfort Controller (factory setting +35 °C) |
| Operating temperature range | 10 °C...55 °C<br>50 °F...131 °F |
| Storage temperature range | -40 °C...70 °C<br>-40 °F...158 °F |

# Features

| | |
|---|---|
| Setting range | 20 °C...55 °C<br>68 °F...131 °F |
| Rated power Pel | Rated power L35 L35/50 Hz: 1.7 kW<br>Rated power L35 L35/60 Hz: 2.03 kW<br>Rated power L35 L50/50 Hz: 1.84 kW<br>Rated power L35 L50/60 Hz: 2.31 kW |
| Permissible operating pressure (p. max.) | 28 bar<br>406.1 PSI |
| Pre-fuse | Motor circuit-breaker: 6.3...10 A |
| Packaging unit | 1 pc(s). |
| Net weight | 73.15 kg |
| Gross weight | 92 kg |
| CRA risk class | Default (Low Risk) |
| Customs tariff number | 84158200 |
| ETIM 9 | EC000855 |
| ETIM 8 | EC000855 |
| ECLASS 8.0 | 27180704 |
| Product description | SK cooling unit Blue e, roof-mounted, 12966 BTU/h, 400-460 V, 3~, 50/60 Hz, carbon steel, WHD: 796 x 470 x 580 mm |

# Approvals

| | |
|---|---|
| Approvals | 30 - KC Korea<br>UL + C-UL (listed)<br>UL + C-UL - FTTA |
| Explanations | Declaration of conformity<br>Declaration of conformity - F-gas regulation<br>Declaration of conformity UK |