
Rittal – The System.

Faster – better – everywhere.





SV 3451.500 Conductor terminal

State: 12/1/2025 (Source: rittal.com/us-en)



SV 3451.500 - Conductor terminal

For connecting round conductors and laminated copper bars.

Features

| Model No. | SV 3451.500 |
|---|--|
| Product description | For connecting round conductors and laminated copper bars. |
| Material | Carbon steel |
| Surface finish | Zinc-plated, passivated |
| Clamping area for laminated copper bars (W x H) | 8 x 8 mm 0.31 x 0.31 ″ |
| Note | Wire end ferrules should be used with fine stranded wire conductors |
| Connection of round conductors | 2.5 - 16 mm² |
| For busbar thickness | 5 mm 0.2 ″ |
| Packaging unit | 15 pc(s). |
| Net weight | 0.375 |
| Gross weight | 0.44 |
| PCF/VE (cradle-to-gate) | 1.6 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 85369010 |
| EAN | 4028177042681 |
| ETIM 9 | EC000001 |
| ETIM 8 | EC000001 |
| ECLASS 8.0 | 27141146 |
| | |

© Rittal 2025

Approvals

| Approvals | UR + C-UR (recognized) |
|--------------|------------------------------|
| Explanations | Declaration of conformity |
| | Declaration of conformity UK |

© Rittal 2025 3