


Rittal – The System.

Faster – better – everywhere.



SV 3452.500

Conductor terminal

State: 2/8/2026 (Source: rittal.com/us-en)



FRIEDHELM LOH GROUP

SV 3452.500 - Conductor terminal

For connecting round conductors and laminated copper bars.

Features

Model No.	SV 3452.500
Product description	For connecting round conductors and laminated copper bars.
Material	Carbon steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	10.5 x 11 mm 0.41 x 0.43 "
Note	Wire end ferrules should be used with fine stranded wire conductors
Connection of round conductors	16 - 50 mm ²
For busbar thickness	5 mm 0.2 "
Packaging unit	15 pc(s).
Net weight	0.81
Gross weight	1.004
PCF/VE (cradle-to-gate)	3.9 kg CO ₂ eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	85369010
EAN	4028177042698
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK