


Rittal – The System.

Faster – better – everywhere.



SV 3452.500 Conductor terminal

State: 5/19/2024 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3452.500 - Conductor terminal

For connecting round conductors and laminated copper bars.

Features

Model No.	SV 3452.500
Product description	For connecting round conductors and laminated copper bars.
Material	Carbon steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	10.5 x 11 mm 0.41 x 0.43 "
Note	Wire end ferrules should be used with fine stranded wire conductors
Connection for round conductor cross-sections	16 - 50 mm ²
For busbar thickness	5 mm 0.2 "
Packaging unit	15 pc(s).
Weight/packaging unit	1.02 kg 2.2 lb.
Customs tariff number	85369010
EAN	4028177042698
ETIM 7.0	EC000001
ECLASS 8.0	27141146

Approvals

Approvals	C-UR UR + C-UR (recognized)
-----------	--------------------------------

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK