
Rittal – The System.

Faster – better – everywhere.



SV 3454.500

Conductor terminal

State: 11/12/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 3454.500 - Conductor terminal

For connecting round conductors and laminated copper bars.

Features

Model No.	SV 3454.500
Product description	For connecting round conductors and laminated copper bars.
Material	Carbon steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	22.5 x 20 mm 0.89 x 0.79 ″
Note	Wire end ferrules should be used with fine stranded wire conductors
Connection of round conductors	70 - 185 mm²
For busbar thickness	5 mm 0.2 ″
Packaging unit	15 pc(s).
Net weight	1.95 kg
Gross weight	1.982 kg
PCF/VE (cradle-to-gate)	7.6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	85369010
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146
Product description	SV Conductor connection clamp, 70-185 mm², clamping area WH: 22,5x20 mm, for bar thickness 5 mm

© Rittal 2026

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK