

Rittal – The System.

Faster – better – everywhere.



SK 3489.640

Wall-mounted cooling unit Blue e+

State: 6/10/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3489.640 - Wall-mounted cooling unit Blue e+ 5459.43 - 18766.8 BTU/h

Energy-efficient Blue e+ wall-mounted cooling units in the 5459.43 - 18766.78 BTU/h power classes. By using speed-controlled components and heat pipe technology, they achieve an average energy saving of 75%. Available in carbon steel and stainless steel.



Features

Model No.	SK 3489.640
Version	wall-mounted
Benefits	<p>An average of 75% energy savings due to speed-regulated components and heat pipe technology</p> <p>Suitable for international use due to a unique multi-voltage capability</p> <p>Longer service life of the components inside the enclosure and the cooling unit due to component-friendly cooling</p> <p>Intuitive operation due to touch display and intelligent interfaces</p>
Product changes	<p>The cover for the connection box for protection for the electrical connection on the cooling unit has not been included in the delivery scope since the start of 2024. Cover 3355.200 and cover 3355.210 can be ordered as an optional accessory.</p>
Material	Stainless steel 1.4301 (AISI 304)
Color	RAL 9007
Supply includes	<p>Condenser with hydrophobic RiNano coating</p> <p>Integral electric condensate evaporation</p> <p>Assembly components</p> <p>Wired ready for connection (plug-in terminal strip)</p>

Features

Options	For remote monitoring and networking of cooling units and chillers, use the Blue e+ Generation IoT Interface, item number 3124.300. Increase machine availability and process safety by remote monitoring of device data, condition, and system messages.
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 5.5 kW Cooling output L35 L35/60 Hz: 5.5 kW Cooling output L35 L50/50 Hz: 3.8 kW Cooling output L35 L50/60 Hz: 3.8 kW Cooling output L35 L35/50 Hz: 18,767 BTU/h Cooling output L35 L35/60 Hz: 18,767 BTU/h Cooling output L35 L50/50 Hz: 12,966 BTU/h Cooling output L35 L50/60 Hz: 12,966 BTU/h
Rated operating voltage	380 V - 480 V, 3~, 50 Hz/60 Hz
Note	Please observe the assembly instructions. When the software is downloaded, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these license conditions. Only for semi-outdoor use (see instructions for description)
Note on Model No.:	Tolerance: 380 V -10% (342 V) and 480 V +5% (509 V) Full internal mounting not possible
Rated output	2.35 kW
Air throughput (unimpeded air flow)	External circuit: 2,300 m ³ /h Internal circuit: 2,300 m ³ /h External circuit: 1,353.7 cfm Internal circuit: 1,353.7 cfm
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.39 Refrigeration factor L35 L35 (EER) 60 Hz: 2.39
Seasonal energy efficiency ratio (SEER) 50/60 Hz	5.6
Version	wall-mounted
Dimensions	Width: 450 mm Height: 1,600 mm Depth: 393 mm Width: 17.7 " Height: 63 " Depth: 15.5 "

Features

Required mounting cut-out	Width of opening: 433 mm Cut-out height: 1,579 mm Width of opening: 17 " Cut-out height: 62.2 "
Protection category IP to EN 60529	Internal circuit IP 55
Protection category NEMA	UL Type 12 UL Type 3R
Refrigerant/cooling medium	Refrigerant: R-1234yf Quantity: 1.76 kg Refrigerant quantity in compression system: 1.04 kg Refrigerant quantity in heat pipe system: 0.72 kg Global Warming Potential (GWP): 0.5 CO2 equivalent (CO2e): 0 t Refrigerant: R-1234yf Quantity: 3.9 lb.
Temperature control	e+ controller (factory setting +35 °C)
Operating temperature range	-20 °C...60 °C -4 °F...140 °F
Storage temperature range	-40 °C...70 °C -40 °F...158 °F
Operating temperature range of refrigerant circuit (active)	3 °C...60 °C
Operating temperature range of heat pipe	-20 °C...45 °C
Setting range	20 °C...50 °C 68 °F...122 °F
Rated power Pel	Rated power L35 L35/50 Hz: 2.3 kW Rated power L35 L35/60 Hz: 2.3 kW Rated power L35 L50/50 Hz: 2.2 kW Rated power L35 L50/60 Hz: 2.2 kW
Permissible operating pressure (p. max.)	24 bar 348.1 PSI
Packaging unit	1 pc(s).

Features

Net weight	71.2 kg
Gross weight	91 kg
PCF/VE (cradle-to-gate)	422.34 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	84158200
ECLASS 8.0	27180704
Product description	SK Blue e+ cooling unit, wall mounted, 5.5 kW, 380-480 V, 3~, 50-60 Hz, stainless steel, HWD: 1600 x 450 x 393 mm

Approvals

Explanations	Declaration of conformity Declaration of conformity - F-gas regulation PCF-declaration
--------------	--