

# Rittal – The System.

Faster – better – everywhere.



## SV 3509.000

## PLS Special Busbars, E-Cu

State: 4/27/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3509.000 - PLS Special Busbars, E-Cu

Lengths range from 495 mm to 2400 mm.



## Features

|                            |                                    |
|----------------------------|------------------------------------|
| Model No.                  | SV 3509.000                        |
| Material                   | E-Cu                               |
| Bar thickness              | 5 mm<br>0.2 "                      |
| Rated current (max.)       | 684 A                              |
| Cross-section              | 300 mm <sup>2</sup>                |
| Note                       | May be cut to length as required   |
| Busbar type                | Busbar E-Cu                        |
| Suitable for busbar system | PLS 800                            |
| Suitable for Model No.     | 9341.000<br>9341.050               |
| Dimensions                 | Length: 2,400 mm<br>Length: 94.5 " |
| Packaging unit             | 1 pc(s).                           |
| Net weight                 | 6.15 kg                            |

# Features

---

|                              |   |
|------------------------------|---|
| Gross weight                 | 6.18 kg   |
| Copper weight (kg per piece) | 6.24  |
| Customs tariff number        | 74071000  |
| ETIM 9                       | EC001522  |
| ETIM 8                       | EC001522  |
| ECLASS 8.0                   | 27370303  |
| Product description          | SV PLS special busbar E-Cu, L: 2400 mm, PLS 800, bar thickness: 5 mm, 300 mm <sup>2</sup> bar cross-section |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |