
Rittal – The System.

Faster – better – everywhere.






SV 3582.020 Busbars CUPONAL

State: 12/1/2025 (Source: rittal.com/us-en)



SV 3582.020 - Busbars CUPONAL

Copper-coated aluminum busbars.



Features

Model No.	SV 3582.020
Product description	Copper-coated aluminum busbars, suitable for configuring busbar systems with busbar supports SV 9340.000/SV 9340.050.
Material	Aluminum
	Copper
Length	2,400 mm
	94.5 ″
Rated current max.	235 A
Note	The rated current is generated at 65°C rail temperature and 35°C
	ambient temperature
	Correction factor diagram according to DIN EN 43 671
	May be cut to length as required
Standards	DIN EN 13 601
Cross-section	20 mm x 5 mm
	0.79 ″ x 0.2 ″
Dimensions	Length: 2,400 mm
	Length: 94.5 "
Packaging unit	6 pc(s).
Net weight	4.5

© Rittal 2025 2

Features

Gross weight	6.42
Copper weight (kg per piece)	0.35
Customs tariff number	74071000
EAN	4028177686557
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303

Approvals

Explanations	Declaration of conformity
·	Declaration of conformity UK

© Rittal 2025 3