Rittal – The System.

Faster – better – everywhere.



SK 3329.540

Wall-Mounted Cooling Unit TopTherm Blue e

State: 11/15/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3329.540 - Wall-Mounted Cooling Unit TopTherm Blue e 1023.64 - 13,648.6 BTU/h

Energy efficient Blue e wall mounting cooling units in performance classes 1023.64 to 13648.57 BTU/h, and with integrated electrical condensation evaporation for 3412.14 BTU/h and above. Available in the special formats “horizontal” and “flat”.

Features

Model No.	SK 3329.540
Version	wall-mounted
Product description	Energy efficient Blue e wall-mounted cooling units in performance classes 300 W to 4000 W and with integrated electrical condensation evaporation for 1000 W and above.
Benefits	May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers
Material	Carbon steel
Color	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Wired ready for connection (plug-in terminal strip) Drilling template Fasteners Integral electric condensate evaporation
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 2.55 kW Cooling output L35 L35/60 Hz: 2.75 kW Cooling output L35 L50/50 Hz: 1.9 kW Cooling output L35 L50/60 Hz: 2 kW Cooling output L35 L35/50 Hz: 8,701 BTU/h Cooling output L35 L35/60 Hz: 9,383 BTU/h Cooling output L35 L50/50 Hz: 6,483 BTU/h Cooling output L35 L50/60 Hz: 6,824 BTU/h
Rated operating voltage	400 V, 3~, 50 Hz 460 V, 3~, 60 Hz

© Rittal 2026

Features

Rated current max.	At 50 Hz: 3.3 A At 60 Hz: 3.4 A
Start-up current (max.)	At 50 Hz: 6.8 A At 60 Hz: 7.6 A
Air throughput (unimpeded air flow)	External circuit: 1,200 m³/h Internal circuit: 1,200 m³/h External circuit: 706.3 cfm Internal circuit: 706.3 cfm
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.11 Refrigeration factor L35 L35 (EER) 60 Hz: 1.88
Version	wall-mounted
Dimensions	Width: 400 mm Height: 1,580 mm Depth: 295 mm Width: 15.7 ″ Height: 62.2 ″ Depth: 11.6 ″
Protection category IP to EN 60 529	External circuit, IP 34 Internal circuit, IP 54
Protection category NEMA	UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 1.15 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.73 t Refrigerant: R-513A Quantity: 2.5 lb.
Temperature control	e-Comfort Controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C 50 °F...131 °F
Storage temperature range	-40 °C...70 °C -40 °F...158 °F
Setting range	20 °C...55 °C 68 °F...131 °F

Features

Rated power Pel	Rated power L35 L35/50 Hz: 1.19 kW Rated power L35 L35/60 Hz: 1.46 kW Rated power L35 L50/50 Hz: 1.45 kW Rated power L35 L50/60 Hz: 1.75 kW
Permissible operating pressure (p. max.)	28 bar 406.1 PSI
Pre-fuse	Motor circuit-breaker: 6.3...10 A
Packaging unit	1 pc(s).
Net weight	70.3 kg
Gross weight	74 kg
CRA risk class	Default (Low Risk)
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK cooling unit Blue e, wall-mounted, 8701 BTU/h, 400-460 V, 3~, 50/60 Hz, carbon steel, WHD: 400 x 1580 x 295 mm

Approvals

Approvals	30 - KC Korea UL + C-UL (listed) UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK