

Rittal – The System.

Faster – better – everywhere.



SV 3586.020 Busbars CUPONAL

State: 5/15/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3586.020 - Busbars CUPONAL

Copper-coated aluminum busbars.



Features

Model No.	SV 3586.020
Product description	Copper-coated aluminum busbars, suitable for configuring busbar systems with busbar supports SV 9340.000/SV 9340.050.
Material	Aluminum Copper
Rated current max.	493 A
Note	The rated current is generated at 65°C rail temperature and 35°C ambient temperature Correction factor diagram according to DIN EN 43 671 May be cut to length as required
Standards	DIN EN 13 601
Cross-section	30 mm x 10 mm 1.18 " x 0.39 "
Dimensions	Length: 2,400 mm Length: 94.5 "
Packaging unit	3 pc(s).
Net weight	7.5 kg
Gross weight	9.2 kg

Features

Copper weight (kg per piece)	1.05
Customs tariff number	74071000
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303
Product description	SV Busbar CUPONAL, WH: 30x10 mm, L: 2400 mm

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---