

Rittal – The System.

Faster – better – everywhere.



HD 4000.062 Command panel HD

State: 6/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.062 - Command panel HD

Monitors, PC and other components with displays are hygienically and securely protected in the command panel. The roof slope of 30° prevents objects from being collected on top and allows liquid to run off quickly.

Features

Model No.	HD 4000.062
Benefits	Roof slope 30° towards the front Height-adjustable mounting board for screens up to 24" in size Bracket for TFT table height adjustable for screens up to 24"
Material	Housing and door: Stainless steel 1.4301 (AISI 304) HD lock inserts: Stainless steel 1.4404 (AISI 316L) Viewing window: Polycarbonate Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Viewing window: Polycarbonate
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Seal: Blue, dyed (RAL 5010)
Supply includes	Housing of all-round solid construction Door with viewing window and inserted seal R/h door catch Holder for desktop TFT with VESA 75/100 locator
Options	without viewing window Mounting plate instead of mounting board Cut-out for touch panel instead of viewing panel Keyboard Support HD
Dimensions	Width: 810 mm Height, front: 692 mm Height rear: 848 mm Depth: 266 mm Width: 31.9 " Height, front: 27.2 " Height rear: 33.4 " Depth: 10.5 "

Features

Visible area	Viewing window width: 535 mm Viewing window height: 325 mm Viewing window width: 21.1 " Viewing window height: 12.8 "
--------------	--

Material thickness - enclosure	1.5 mm 0.06 "
--------------------------------	------------------

Material thickness - door	2 mm 0.08 "
---------------------------	----------------

Protection category NEMA	NEMA 4X
--------------------------	---------

IK code	IK08
---------	------

Packaging unit	1 pc(s).
----------------	----------

Net weight	33.2 kg
------------	---------

Gross weight	33.2 kg
--------------	---------

PCF/VE (cradle-to-gate)	99.56
-------------------------	-------

Customs tariff number	94032080
-----------------------	----------

ETIM 9	EC000261
--------	----------

ETIM 8	EC000261
--------	----------

ECLASS 8.0	27180101
------------	----------

Approvals

Explanations	PCF-declaration
--------------	-----------------