

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.060

### Clamping frame

State: 9/8/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.060 - Clamping frame

Parallel machining of enclosures in the machining area for cubic parts on the Perforex BC machining center and Perforex Milling Terminal MT for reduced setting-up time and increased productivity.

## Features

Model No.	AS 4050.060
Version	Pneumatic clamping device
Product description	Enables enclosures to be processed simultaneously in the cube machining area of the Perforex machining center BC and Perforex Milling Terminal MT.
Possible number of terminal Boxes for parallel processing	3
Note	The use of the clamping frame (Model No. 4050.080) with the BC machining center (Model No. 4050.230) is only possible with the two-door variant.
Suitable for Model No.	4050.101 4055.910 4055.911
Suitable for	Perforex BC 1001 HS Perforex MT 1101 Perforex MT 1101 S
Dimensions of clampable enclosures max.	Width: 200 mm Height: 300 mm Depth: 300 mm
Dimensions of clampable enclosures min.	Width: 85 mm Height: 70 mm Depth: 70 mm
Packaging unit	1 pc(s).
Net weight	25
Gross weight	25
Customs tariff number	84669360

# Features

EAN	4028177804302
ETIM 9	EC003010
ETIM 8	EC003010
ECLASS 8.0	36609190