

Rittal – The System.

Faster – better – everywhere.



AS 4050.150 Assembly frame

State: 4/26/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.150 - Assembly frame

The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for the mounting of plates and enclosures.

Features

| | |
|---------------------------------|--|
| Model No. | AS 4050.150 |
| Version | 150 MN (manually tilt-adjustable) |
| Product description | The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for the mounting of plates and enclosures. |
| Benefits | Allows ergonomic and back-friendly working Individually positionable in the workshop, as it is independent from the power network Minimal space required when not in use Easy handling thanks to four casters including complete locking function Variable fixing of mounting plates using quick-release fasteners |
| Technical specifications | Incline can be adjusted from approximately 0 – 80° |
| Supply includes | Assembly frame 1 VE clamping unit at bottom 1 packing unit with top clamping unit |
| Note | With the assembly frame extension, a maximum machining area of 1900 x 1900 mm can be achieved. |
| Machine dimensions | Width: 1,400 mm Depth: 1,250 mm |
| Dimensions support surface max. | Width: 1,110 mm Height: 1,900 mm |
| Dimensions support surface min. | Width: 1,110 mm Height: 1,230 mm |
| Load | 150 kg 330.7 lb. |

Features

| | |
|-----------------------|--|
| Working height | Working height (min.): 100 cm Working height (max.): 100 cm |
| Packaging unit | 1 pc(s). |
| Net weight | 123 kg |
| Gross weight | 138 kg |
| Customs tariff number | 84279000 |
| ETIM 9 | EC002224 |
| ETIM 8 | EC002224 |
| ECLASS 8.0 | 36659090 |
| Product description | Assembly frame 150 MN |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|