


Rittal – The System.

Faster – better – everywhere.



AS 4050.435

Wiring duct cutter MC125

State: 12/2/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.435 - Wiring duct cutter MC125

For the manual cutting of wiring ducts, with adjustable length stop for the material being cut. Anodized contact surface with laser-engraved marking in millimeters and inch scales. Safe machining due to integrated finger guard. Designed for mounting on a workbench.



Features

Model No.	AS 4050.435
Product description	For the manual cutting of wiring ducts, with adjustable length stop for the material being cut. Anodized contact surface with laser-engraved marking in millimeters and inch scales. Safe machining due to integrated finger guard. Designed for mounting on a workbench.
Benefits	Enables economic manual cable duct cutting Easier for cutting wiring ducts to length compared to sawing by hand
Support area	Width: 1,332 mm Height: 798 mm Depth: 405 mm Width: 52.4 ~ Depth: 15.9 ~
Insertion height (max.)	28 mm

Features

Machinable wall thickness of cable ducts (max.)	2.5 mm
---	--------

Maximum workable width, cable duct	125 mm
------------------------------------	--------

Workable material	Plastic
-------------------	---------

Packaging unit	1 pc(s).
----------------	----------

Net weight	14.3
------------	------

Gross weight	15.43
--------------	-------

Customs tariff number	84778095
-----------------------	----------

EAN	4028177930933
-----	---------------

ETIM 9	EC002778
--------	----------

ETIM 8	EC002778
--------	----------

ECLASS 8.0	17139290
------------	----------
