

Rittal – The System.

Faster – better – everywhere.



AS 4050.435

Wiring duct cutter MC125

State: 4/3/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.435 - Wiring duct cutter MC125

For the manual cutting of wiring ducts, with adjustable length stop for the material being cut. Anodized contact surface with laser-engraved marking in millimeters and inch scales. Safe machining due to integrated finger guard. Designed for mounting on a workbench.



Features

Model No.	AS 4050.435
Product description	For the manual cutting of wiring ducts, with adjustable length stop for the material being cut. Anodized contact surface with laser-engraved marking in millimeters and inch scales. Safe machining due to integrated finger guard. Designed for mounting on a workbench.
Benefits	Enables economic manual cable duct cutting Easier for cutting wiring ducts to length compared to sawing by hand
Support area	Width: 1,332 mm Height: 798 mm Depth: 405 mm Width: 52.4 " Depth: 15.9 "
Insertion height (max.)	28 mm

Features

Machinable wall thickness of cable ducts (max.)	2.5 mm
Maximum workable width, cable duct	125 mm
Workable material	Plastic
Packaging unit	1 pc(s).
Net weight	14.3 kg
Gross weight	15.43 kg
Customs tariff number	84778095
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	17139290
Product description	Wire duct cutter MC125 for manual cutting of wire ducts and their covers