

**Rittal – The System.**

Faster – better – everywhere.



**AS 4050.435**

**Wiring duct cutter MC125**

State: 2/2/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AS 4050.435 - Wiring duct cutter MC125

For the manual cutting of wiring ducts, with adjustable length stop for the material being cut. Anodized contact surface with laser-engraved marking in millimeters and inch scales. Safe machining due to integrated finger guard. Designed for mounting on a workbench.



## Features

Model No.	AS 4050.435
Product description	For the manual cutting of wiring ducts, with adjustable length stop for the material being cut. Anodized contact surface with laser-engraved marking in millimeters and inch scales. Safe machining due to integrated finger guard. Designed for mounting on a workbench.
Benefits	Enables economic manual cable duct cutting Easier for cutting wiring ducts to length compared to sawing by hand
Support area	Width: 1,332 mm Height: 798 mm Depth: 405 mm Width: 52.4 " Depth: 15.9 "
Insertion height (max.)	28 mm

# Features

---

Machinable wall thickness of cable ducts (max.) 2.5 mm

---

Maximum workable width, cable duct 125 mm

---

Workable material Plastic

---

Packaging unit 1 pc(s).

---

Net weight 14.3

---

Gross weight 15.43

---

Customs tariff number 84778095

---

EAN 4028177930933

---

ETIM 9 EC002778

---

ETIM 8 EC002778

---

ECLASS 8.0 17139290