

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.437

## DIN support rail cutter MC3

State: 6/15/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.437 - DIN support rail cutter MC3

Manual profile cutter for burr-free cutting of 30/15 C-profile rails as well as TS 35/7.5 and TS 35/15 support rails. The desired length of the rail can be precisely and repeatedly adjusted with the ruler (mm/inch) and the adjustable stop. For mounting on the workbench.



## Features

Model No.	AS 4050.437
Product description	Manual profile cutter for burr-free cutting of 30/15 C-profile rails as well as TS 35/7.5 and TS 35/15 support rails. The desired length of the rail can be precisely and repeatedly adjusted with the ruler (mm/inch) and the adjustable stop. For mounting on the workbench.
Benefits	Cost-effective manual cutting of profile and mounting rails Easier to cut profile and support rails to the correct length than sawing by hand Easy burr-free cutting with eccentric lever Low-maintenance and durable
Support area	Width: 1,343 mm Height: 1,162 mm Depth: 312 mm Width: 52.9 " Depth: 12.3 "
Workable material	Carbon steel Aluminum Copper
Packaging unit	1 pc(s).
Net weight	15 kg
Gross weight	16.15 kg

# Features

---

Customs tariff number	73269098
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890
Product description	For cutting iron, copper and aluminium up to 1.2 mm thickness, plastic up to max. 2.0 mm thickness, cutting width 2.7 mm

---